

Electronic transformers



Type: EST70/12.480 240V 50/60Hz
Item number: 176497

LiteLine

Casing: Heat-resistant polycarbonate
Max. permitted casing temperature: 75°C
Output voltage Secondary: 11,5 V
Mains frequency: 50-60 Hz
Power factor: 0,98
Efficiency: 95%
Nominal current: 0,29 A
Screw terminals: 2,5 mm²



Output [W]: 70
Main voltage AC [V]: 240
Version: Compact plastic casing LiteLine
Dimming: Phase-cutting leading-edge and trailing-edge dimmer
Kind of connection: Screw terminal
Protection class: Class of protection II
Width B [mm]: 37
Height [mm]: 28
Length [mm]: 128
Fixing centre [mm]: 117
Max. ambient temperature [°C]: 45

Unit: 36 pcs.

Overtemperature-protection, Overload protection and protection against short-circuit over thermal cut-out with automatic restart
EN 61046 (Safety)
EN 61047 (Performance)
EN 61000-3-2 (Mains harmonics)
EN 55015 (Radio-frequency interference suppression)
EN 61547 (EMC immunity to interference)

