

Electronic transformers

Type: EST105/12.481 240V 50/60Hz

Item number: 176498 FP

LiteLine

Casing Heat resistant polyamide
 Max. permitted casing temperature: 85°C
 Output voltage Secondary: 11,5 V
 Mains frequency: 50-60 Hz
 Power factor: 0,98
 Efficiency: 95%
 Nominal current: 0,43 A
 Screw terminals: 2,5 mm²

With 1.5 metre flex and plug

Output:	105VA
Main voltage AC:	240V
Version:	Compact plastic casing LiteLine
Dimming:	Phase-cutting trailing-edge and leading-edge dimmer
Kind of connection:	2
Protection class:	For luminaires of protection class II
Width B:	37mm
Height:	28mm
Length:	128mm
Fixing centre:	117mm
Max. ambient temperature:	40 ⁰ C

Unit: 36 pcs.

Overtemperature protection, overload protection and protection against short circuit over thermal cut-out with automatic restart

EN 61046 (Safety)
 EN 61047 (Working method)
 EN 61000-3-2 (Mains harmonics)
 EN 55015 (Radio-frequency interference suppression)
 EN 61547 (EMV Immunity to interference)

