

## Datasheet for 76650-0019

### General Information

<b>Kit Part Number:</b>	76650-0019
<b>Connector Type:</b>	Wire-to-Wire
<b>Solution:</b>	Power Connectors
<b>Molex Family:</b>	Standard .062
<b>Certificates:</b>	N/A
<b>Country of Origin:</b>	Kit assembled in U.S.A

### Specifications

<b>Circuit Size:</b>	1, 12, 15, 2, 3, 36, 4, 5, 6, 9
<b>Current Rating:</b>	5A
<b>Mounting Style:</b>	Free-Hanging, Panel Mount
<b>Orientation:</b>	Panel Mount Plugs, Receptacles
<b>Pitch:</b>	3.68mm (.145")
<b>Tool Included:</b>	Yes
<b>Voltage Rating:</b>	250V
<b>Wire Gauge (AWG):</b>	24-18

### Product Highlights

The Standard .062" is a durable and economical power or signal connector, capable of carrying up to 5.0 amps per circuit. Tough Nylon housings and robust terminal design create a durable, long lasting product. The Standard .062" products are reliable and offer high value in features and price. These products are an excellent choice for power or signal interconnect applications.

#### Features and Benefits

- Male and female terminals may be used in either plug or receptacle housings
- Free hanging or panel mount housing version available
- Round terminals may be oriented in any direction for fast assembly
- Passive (friction lock)
- Polarized housing assures proper mating

#### Applications

- Power Supplies
- Appliances
- Gaming Machines
- Vending Machines
- Refrigerators
- Washing Machines
- Copy Machines

## Bill of Materials

Molex Part No.	Description	Quantity
02-06-2103	1.57mm (.062") Diameter Male Crimp Terminal, 24-18 AWG	100
02-06-1103	1.57mm (.062") Diameter Female Crimp Terminal, 24-18 AWG	100
03-06-1011	3.68mm (.145") Pitch, 1 Circuit, Free-Hanging Pin and Socket Receptacle	15
03-06-1022	3.68mm (.145") Pitch, 2 Circuit, Panel Mount Pin and Socket Receptacle	5
03-06-1038	3.68mm (.145") Pitch, 3 Circuit, Panel Mount Pin and Socket Receptacle	5
50-29-1758	3.68mm (.145") Pitch, 4 Circuits, Panel Mount Pin and Socket Receptacle	3
03-06-1055	3.68mm (.145") Pitch, 5 Circuit, Panel Mount Pin and Socket Receptacle	3
03-06-1061	3.68mm (.145") Pitch, 6 Circuit, Panel Mount Pin and Socket Receptacle	4
03-06-1121	3.68mm (.145") Pitch, 12 Circuit, Panel Mount Pin and Socket Receptacle	2
03-06-1361	4.19mm (.165") Pitch, 36 Circuit, Panel Mount Pin and Socket Receptacle	1
03-06-2011	3.68mm (.145") Pitch, 1 Circuit, Free-Hanging Pin and Socket Plug	15
03-06-2024	3.68mm (.145") Pitch, 2 Circuit, Panel Mount Pin and Socket Plug	5
03-06-2033	3.68mm (.145") Pitch, 3 Circuit, Panel Mount Pin and Socket Plug	5
03-06-2041	3.68mm (.145") Pitch, 4 Circuit, Panel Mount Pin and Socket Plug	3
03-06-2054	3.68mm (.145") Pitch, 5 Circuit, Panel Mount Pin and Socket Plug	4
03-06-2062	3.68mm (.145") Pitch, 5 Circuit, Panel Mount Pin and Socket Plug	4
03-06-2091	3.68mm (.145") Pitch, 9 Circuit, Panel Mount Pin and Socket Plug	3
03-06-2121	3.68mm (.145") Pitch, 12 Circuit, Panel Mount Pin and Socket Plug	2
03-06-2151	3.68mm (.145") Pitch, 15 Circuit, Panel Mount Pin and Socket Plug	1
03-06-2361	4.19mm (.165") Pitch, 36 Circuit, Panel Mount Pin and Socket Plug	1
03-06-6155	3.68mm (.145") Pitch, 15 Circuit, Panel Mount Pin and Socket Receptacle	1
W-HT-1921	Universal Crimping Tool	1
W-HT-2023	Extraction Tool	1
50-36-1871	9 Circuit, Panel Mount Nylon Connector Receptacle	3

## Recommended Molex Tool

Molex Part No.	Description
W-HT-1921 (included in kit)	No Additional Information
63811-1000 (not included in kit)	<a href="#">Click for more info</a>