

http://www.molexkits.com

Datasheet for 76650-0072

General Information

Kit Part Number: 76650-0072

Connector Type: Wire-to-Wire

Solution: Power Connectors

Molex Family: Standard .093

Certificates: N/A

Country of Origin: Kit assembled in U.S.A

Specifications

Circuit Size: 5

Current Rating: 5A

Mounting Style: Free-Hanging, Panel Mount

Orientation: Plugs, Receptacles

Pitch: 5.03mm (.198")

Tool Included: No
Voltage Rating: 600V
Wire Gauge (AWG): 22-18

Product Hightlights

The Standard 2.36mm (.093") is a durable and economical power or signal connector, capable of carrying up to 12 amps per circuit. Tough Nylon housings and robust terminal design create a durable, long lasting product. The Standard .093" products are reliable and offer high value in features and price. These products are an excellent choice for power or signal interconnect applications. Â Features and Benefits • Male and female terminals may be used in either plug or receptacle housings • Free hanging or panel mount housing version available • Round terminals may be oriented in any direction for fast assembly Â Applications • Power Supplies • Appliances • Gaming Machines • Vending Machines • Refrigerators • Washing Machines • Copy Machines



http://www.molexkits.com

Bill of Materials			
Molex Part No.	Description	Quantity	
02-09-1119	2.36mm (.093") Diameter Crimp Female Socket Terminal, 22-18 AWG	12	
02-09-2118	.093" Diameter Crimp Male Pin Terminal, 22-18 AWG	12	
03-09-1054	5 Circuit, Panel Mount Nylon Connector Receptacle	2	
03-09-2057	5 Circuit, Panel Mount Nylon Connector Plug	2	

Recommended Molex Tool			
Molex Part No.	Descripition		
63819-1200 (not included in kit)	Click for more info		
11-02-0003 (not included in kit)	Click for more info		