

BETADUCT

Betaduct Ltd

Newtown Trading Estate,
Northway Lane, Tewkesbury,
Gloucestershire
GL20 8JG

Technical Specifications -



PRODUCT

BETADUCT

PART NUMBER

Please see Betaduct Ltd Brochure for full details

SIZES

Nominal internal mm (width x height)
25x50 37.5x50 50x50 75x75 100x75 100x125
25x75 37.5x75 50x75 75x100 100x100
25x100 37.5x100 125x75
All supplied in standard 2 metre lengths with lids

SLOTTING

Open, Narrow, Closed and Solid

CAPACITY

Recommended 55% maximum (See Betaduct Capacity Chart)

MATERIAL

Self extinguishing lead free PVC

COLOUR

Grey, Black, White and Blue for Intrinsically Safe Circuits

SERVICE TEMPERATURE RANGE

- 15°C to +65°C

APPLICATION

Control panel trunking for speedy lead out of wiring through open side slots.

FIRE HAZARD PERFORMANCE FLAMMABILITY

UL94V-0 rated material.

CHEMICAL RESISTANCE

Ammonium Hydroxide, Chlorine, Diesel, Detergents, Ethanol, Hydrochloric acid, Inorganic solvents, Mineral oils, White spirit.

APPROVALS

cULsa (Combined), Lloyds Register and Rolls-Royce

STANDARDS

Base slots to DIN 43659

All technical data is believed to be accurate and is provided for information and guidance only
© Betaduct Ltd®

www.betaduct.co.uk

Tel +44 (0)1684 274274

Fax +44 (0)1684 276266

Betaduct Ltd provides the most comprehensive range of cable management systems in the UK to both the OEM and retro fit market.

