# **KILOWATT HOUR METERS**



**DESCRIPTION** DIN96 meters for measuring kWh of individual machines or complete systems.

**APPLICATION** For monitoring the consumption of electricity in single or three phase systems. Savings can be made by monitoring and using electricity at the optimum time.




### 96 kWh METERS



Manufactured to BS5685, IEC521 with a class accuracy of 1% to IEC1036, and supplied in a 96 x 96mm DIN case. The product has a 7 digit non resettable mechanical counter.

Pulsed output is available to send to PLC's, data loggers and computers. Analogue mA output is also available.

#### Dimensions (mm)



## **RANGE**

Description	Product Codes
Single Phase	D96kWh1
3ph 3W balanced load	D96kWh2
3ph 4W balanced load	D96kWh3
3ph 3W unbalanced load	D96kWh4
3ph 4W unbalanced load	D96kWh9

#### **Ordering Information**

- Product Code
- Current Transformer Ratio
- Voltage Transformer Ratio
- Frequency
- Auxiliary Voltage

#### **Options**

- Pulsed output (0.1, 1 or 10 per kWh)
- Analogue output
- Non standard pulse width
- Calibration at temp. other than 23°C
- Calibration at Hz 35-450

kWh meters are also available in DIN rail 100mm cases

## **Technical Specification**

**Rated current:** 1 or 5A (<0.2VA / phase burden).

Range: 10-120% of rated current. Overload: 4 x rated current continuous. 50 x rated current for 1 sec.

Rated voltage: 57-500V (<0.2VA / phase burden).

Range: 80-120% of rated voltage. Overload: 1.5 x rated voltage continuous.

4 x rated voltage for 1 sec.

**Frequency:** 50 or 60Hz nominal range. Auxiliary: 115/230/400 AC Voltage.

Pulsed output: Normally open volt free contact,

50V 150mA 5W AC/DC.

Pulse rate: 0.1, 1 or 10 per kWh. Pulse duration: 250msec standard.

**Analogue output:** Rated value: 0-1mA into <5k Ohms.

0-20mA into <250k Ohms.

Accuracy: Class 1 to IEC 1036.

Operating temp: -25°C to +70°C. Temp coefficient: 0.01% per 1°C.

Material: Polycarbonate to UL94V0.

Enclosure: IP 54.

Mounting: 4 side brackets & screws.

Our policy is one of continuous development and therefore specifications may change without notice.

### **HOWARD BUTLER LTD**

CROWN WORKS, LINCOLN ROAD WALSALL WS1 2EB ENGLAND

Tel: 01922 640003 Fax: 01922 723626

International Tel: +44 1922 640003 E-mail: sales@hobut.co.uk

Web: www.hobut.co.uk