



Wiha. Premium Tools
for Professionals.

Wiha Square Handle. The Classic Screwdriver for Multiple Applications.



*Wiha Square handle,
impact resistant and
cadmium-free –
also withstands a few
hammer strokes.*



Square Handle Advantages:

- Robust, large-surface handle made of impact-resistant plastic material, chemical and oil-resistant
- Smooth handle surface allows easy cleaning
- Wiha ChromeTop-finish on tip for a perfect fit every time
- Takes up a small amount of space in the toolbox

The Wiha Square handle screwdriver is the classic screwdriver for everyday use in multiple applications.

Its robust handle is manufactured from high quality plastic and is impact-resistant, non-splintering and recyclable.

Users appreciate its multiplicity and high quality, which is also expressed through the hardened chrome-vanadium-molybdenum steel blade.





Wiha. Premium Tools
for Professionals.

Wiha Square Handle. The Classic Screwdriver for Multiple Applications.

For Slotted Screws.



148 Slotted Screwdriver.
Blade: **Round blade.**
Chrome-vanadium steel, through hardened, nickel-plated.
Anti-Cam-Out ribs on tips from size 5.5.
Handle: Wiha Square handle, oil and grease resistant.
Application: Traditional square handle design for everyday use in multiple applications.

Order-No.	Ø	Length	Tip Length	Tip Dia	Tip Length	Tip Dia	Tip Length
00097 4	2.5	75	0.4	150	3.5	19	10
00098 1	3.5	90	0.5	175	4.0	22	10
00099 8	4.5	100	0.7	195	5.0	24	10
00100 1	5.5	120	0.95	225	6.0	28	10
00101 8	7.0	140	1.05	255	7.0	32	10
00102 5	9.0	160	1.2	275	8.0	32	10
00103 2	10.0	180	1.4	305	8.0	36	10
00104 9	12.0	200	1.75	325	10.0	36	5



172 Slotted Screwdriver.
Blade: **Round blade, hex bolster for additional torque.**
Chrome-vanadium steel, through hardened, nickel-plated.
Anti-Cam-Out ribs on tips from size 5.5.
Handle: Wiha Square handle, oil and grease resistant.
Application: Traditional square handle design for everyday use in multiple applications.

Order-No.	Ø	Length	Tip Length	Tip Dia	Tip Length	Tip Dia	Tip Length
00176 6	3.5	75	0.6	160	4.0	-	22 10
00177 3	4.5	90	0.8	185	5.0	-	24 10
00178 0	5.5	100	0.95	205	5.5	8	28 10
00180 3	7.0	125	0.95	230	6.0	10	28 10
00182 7	9.0	150	1.1	265	7.0	10	32 10
00184 1	10.0	175	1.2	290	8.0	13	32 10
00186 5	12.0	200	1.4	325	8.0	13	36 5
00187 2	14.0	250	1.75	375	10.0	17	36 5

For Slotted Screws.



186 Slotted (Cabinet) Screwdriver.
Blade: **Round blade.**
Chrome-vanadium steel, through hardened, nickel-plated.
Anti-Cam-Out ribs on tips from size 5.5.
Handle: Wiha Square handle, oil and grease resistant.
Application: Traditional square handle design for everyday use in multiple applications.
Extra: Series includes extra long dimensions for screws in difficult to reach locations.

Order-No.	Ø	Length	Tip Length	Tip Dia	Tip Length	Tip Dia	Tip Length
00201 5	2.0	40	0.4	100	2.0	14	10
00202 2	2.0	60	0.4	120	2.0	14	10
00203 9	2.5	50	0.4	110	2.5	14	10
00204 6	2.5	75	0.4	150	2.5	19	10
00206 0	3.0	75	0.5	150	3.0	19	10
00207 7	3.0	100	0.5	175	3.0	19	10
00208 4	3.0	150	0.5	225	3.0	19	10
00209 1	3.0	200	0.5	285	3.0	22	10
00210 7	3.0	300	0.5	385	3.0	22	5 108-708
00211 4	3.5	100	0.6	175	3.5	19	10
00212 1	4.0	100	0.8	185	4.0	22	10
00213 8	4.0	150	0.8	235	4.0	22	10
00214 5	4.0	200	0.8	285	4.0	22	10
00215 2	4.0	300	0.8	385	4.0	22	5 108-709
00218 3	5.0	100	0.9	195	5.0	24	10
00219 0	5.0	150	0.9	245	5.0	24	10
00220 6	5.0	200	0.9	295	5.0	24	10
00221 3	5.0	300	0.9	395	5.0	24	5 107-710
00222 0	5.5	100	1.0	195	5.5	24	10
00223 7	5.5	150	1.0	245	5.5	24	10
00224 4	5.5	200	1.0	295	5.5	24	10
00226 8	6.0	100	1.1	205	6.0	28	10
00227 5	6.0	150	1.1	255	6.0	28	10
00228 2	6.0	200	1.1	305	6.0	28	10
00229 9	6.0	300	1.1	405	6.0	28	5
00230 5	7.0	150	1.2	255	6.0	28	10
00231 2	8.0	150	1.2	265	7.0	32	10
00232 9	8.0	200	1.2	315	7.0	32	5
00234 3	8.0	300	1.2	415	7.0	32	5 108-711
00235 0	10.0	200	1.6	315	8.0	32	5
00236 7	10.0	300	1.6	415	8.0	32	5
00237 4	10.0	500	1.6	615	8.0	32	5