


Wiha-PicoFinisi





The soft material of the handle, together with the rotating cap, enables optimum and sensitive twisting.

The clear marking of the drive on the rotating cap provides easy and fast identification of the required screwdriver.



The Wiha PicoFinish screwdrivers are predestined for high-precision work, predominantly with electro-technical and precision components.


The octagonal rapid-rotation zone at the front of the handle allows rapid twisting.

The extraordinarily easy-to-twist rotating cap permits the delicate turning of fine screws with just one hand.



### **PicoFinish Advantages:**

- · Special soft plastic material assures comfortable, delicate work
- Ideal for fine adjustments in electronic assembly work and precision applications, as well as for hobby use and model making
- Clear marking of the drive on the rotating cap provides easy and fast identification of the required screwdriver
- Convex handle end allows the transmission of a controlled high torque to powerfully tighten or loosen the screw head



- Palm saving rotating cap with a large surface for the fingers makes incremental adjustment easy
- Wiha ChromeTop-finish on tip for a perfect fit every time



## Wiha PicoFinish. The Specialist for Precision Applications.

### For Hex Nuts.

# With PicoFinish 205

265 P Nut Driver.

Handle:

With rotating cap and rapid-turning zone.

Blade: Chrome-vanadium steel, through hardened, chrome-plated.

Wiha PicoFinish handle for rapid rotation.

Application: Ideal for high-precision work with electro-technical and precision

components.

Order-No.	Ot	÷100-	- <del>-</del> -	==		-+	-	
005443	1.5	2.5	3.0	60	160	18	10	310-6202
00545 0	1.8	2.9	3.5	60	160	18	10	310-6214
00546 7	2	3.2	4.0	60	160	18	10	C 18.13.
00547 4	2.5	4.0	4.0	60	160	18	10	310-6226
00548 1	3	5.0	5.0	60	160	18	10	310-6238
005498	3.2	5.0	5.0	60	160	18	10	
00550 4	3.5	5.3	6.0	60	160	18	10	310-6240
00551 1	4	5.5	6.0	60	160	18	10	310-6251
005528	4.5	6.2	7.0	60	160	18	10	310-6263
00553 5	5	6.8	7.0	60	160	18	10	310 - 6275
00554 2	5.5	7.6	8.0	60	160	18	10	Europa President
00555 9	6	8.2	9.0	60	160	18	10	
00556 6	7	9.6	10.0	60	160	18	10	
00000	1	9.0	10.0	00	100	10	10	The Annual Public

#### 265 P Zoll Nut Driver.

With rotating cap and rapid-turning zone. Inch sizes.

Order-No.	01 =		==	-÷	-	
00561 0	3/32"	60	160	18	10	
00564 1	7/64"	60	160	18	10	
00559 7	1/8"	60	160	18	10	
00565 8	9/64"	60	160	18	10	
00562 7	5/32"	60	160	18	10	
00560 3	3/16"	60	160	18	10	
00563 4	7/32"	60	160	18	10	
00558 0	1/4"	60	160	18	10	

## Chip Lifter.



268 10 P Chip Lifter.

Blade: High quality chrome-vanadium-molybdenum steel, through

hardened, chrome-plated.

Handle: Wiha PicoFinish handle.

Application: For lifting tight parts on circuit boards.

Order-No.	:3	13	==	===			
00574 0	1	3.5	50	150	18	5	