

## Wiha Bit Holders with Handle.

## Bit Holder 1/4".

## Bit Holder 1/4".



Bit holder 1/4", with hex shaft.

Handle: Wiha SoftFinish® multi-component handle with roll of protection.

Bitholder: Made from rust proof steel.

Blade: Chrome-vanadium steel, through hardened, nickel plated.

Suitable for: DIN 3126 ISO 1173 Style D 6.3.

Order-No.	O:	==	==	-÷	_	
01475 9	1/4"	125	243	36	10	
014766	1/4"	300	418	36	10	
014773	5/16"	150	274	41	5	



387 Bit holder 1/4",

Handle:

with quick release holder.

Wiha SoftFinish® multi-component handle with roll of protection.

Bitholder: ClicFix quick release holder, magnetic. Suitable for: DIN 3126 ISO 1173 Style D 6.3.

Application: Compact, handy style for working in confined places.

When the bit must be held securely.

Order-No.	O:	==	-=	-+	-	
<b>25874</b> 0	1/4"	35	146	30	10	223 - AVE 10 10



385 Bit holder 1/4",

Handle:

with hex bolster.

Wiha SoftFinish® multi-component handle with roll of protection.

Bitholder: Made from rust proof steel.

Blade: Chrome-vanadium steel, through hardened, nickel plated.

Suitable for: DIN 3126 ISO 1173 Style D 6.3.

Extra: Hex bolster for higher torque.

Order-No.	01	=-	===	O:	<b></b> ÷	-	
01478 0	1/4"	120	238	10	36	10	132-492



526 Bit holder 1/4", with flexible shaft.

Handle: Non-slip Wiha MicroFinish® handle, chemical and oil resistant.

Bitholder: Made from rust proof steel.

Blade: Chrome-vanadium steel, through hardened, nickel plated.

Suitable for: DIN 3126 ISO 1173 Style D 6.3.



## 386 Bit holder 1/4",

with flexible shaft.

Handle: Wiha SoftFinish® multi-component handle with roll of protection.

Bitholder: Made from rust proof steel.

Blade: Plastic coated flexible metal.

Suitable for: DIN 3126 ISO 1173 Style D 6.3.

Extra: For offset screws.

Order-No.	OI .	==	==	<b>-</b> ÷	_	
01479 7	1/4"	150	268	36	10	832-503







Bit holder 1/4",

with flexible shaft.

Handle: Non-slip Wiha MicroFinish® handle, chemical and oil resistant.

Bitholder: Made from rust proof steel.

Blade: Plastic coated flexible metal.

Suitable for: DIN 3126 ISO 1173 Style D 6.3.

Application: For offset screws.

Order-No.	O1	==	==		
<b>04323</b> 0	1/4"	150	270	36	10