

## Technical Specification



### Features

Feature	Description
Audio Sources	6 – Internet Radio, MP3, CD, Terrestrial Radio, Auxiliary Input.
Portable	Yes, two part system. The Internet Radio is completely portable receiving all data and audio over a wireless link from the transmitter part connected to the PC USB port.
LCD Display	20 character 5 x 7 dot matrix display with icons, EL blue backlight.
Power Source	8 x C size 1.5 volt alkaline battery or AC mains – 220 - 240 volt Europe, 110 volt US.
Operation Time	Approx 30 hours continuous play at mid volume on one set of alkaline batteries.

### Amplifier

Feature	Description
Output Power (RMS)	2 x 2.2 watts
Total Power	4.4 watts
Music Power	2 x 4.4 watts
PMPO	65 watts

### Internet Radio

Feature	Description
Radio presets	6 with station name display

### Terrestrial Tuner

Feature	Description
Digital Tuner bands	FM Stereo
Tuner presets	6 for each band
Antenna FM	Yes

Frequency Display	Yes, 4 digit
-------------------	--------------

### Loudspeaker

Feature	Description
No. of way speaker system	1 – way full range driver
Impedance	2 x 8 ohm
Rated Power (RMS)	2 x 6 watts
Size	67 mm x 106 mm, Elliptical
Magnetic Shielding	Yes

### Connections

Feature	Description
Stereo headphone	Yes
Auxiliary Input	Yes, 2 x phono socket
Auxiliary Output	Yes, 2 x phono socket
USB connection	Yes, transmitter connects to PC USB port with 1.5 metre cable

### Wireless Link

Feature	Description
Stereo Audio Channel	Europe 863 MHz 10 mW erp, USA 925 MHz 10 mW erp, user selectable band switching to avoid interference.
Data Channel	Europe + USA, 433 MHz , bi-directional, user selectable band switching to avoid interference.

### Dimensions

Feature	Description
Radio Remote Module	Front to Back 155mm (6.1"), Side to Side 283mm (11.1"), Height 150mm (5.9")
USB Base Module	Front to Back 120mm (4.7"), Side to Side 135mm (5.3"), Height 41mm (1.6")