

# Omega Vacs

POWERFUL

## THREE FILTRATION OPTIONS

**STANDARD FILTER WITH A 0.3 MICRON RETENTION** - Ideal for soot, pollen, black toner and most color toner.

**HEPA FILTER WITH 99.97% EFFICIENCY AT 0.3 MICRON** - Uses include very fine dust, color toner, fumes, and other ultra fine particulate.

**ULPA FILTER WITH 99.999% EFFICIENCY AT 0.12 MICRON.** Uses in medical, manufacturing, and other processes to extract ultra fine particulate.

**ESD SAFE** - Conductive construction provides maximum static protection to safeguard the operator and sensitive electronic components.



**SELF STORAGE COMPARTMENT** - All accessories store conveniently in the case cover.

**TONER-PROOF 6' HOSE** - Provides continual operation with no clogging. Crush proof.

**FLEXIBLE 16" GOOSE-NECK** - To get to those hard-to-reach places!

**CREVICE TOOL & CREVICE TOOL BRUSH** - To loosen dust and toner particles in tight areas.

## SPECIFICATIONS:

Omega 120 Volt - VACOMEGA  
Omega 120 Volt (HEPA) - VACOMEGACT  
Omega 230 Volt - VACOMEGA220

**DIMENSIONS:**    **LENGTH:** 19 1/4"  
                          **WIDTH:** 7 3/8"  
                          **HEIGHT:** 9 5/16"  
                          **WEIGHT:** 11 LBS.

**120 VOLT MOTOR:** 1.2 PHP, 6.83 AMPS,  
789 WATTS, 60 HZ

**230 VOLT MOTOR:** 1.2 PHP, 3.3 AMPS,  
775 WATTS, 60HZ

**CERTIFICATION:** *Omega 120 VOLT:*  
UL & UL CANADIAN APPROVED

*Omega 230 VOLT:*  
CE & TUV APPROVED

**3 YEAR LIMITED WARRANTY**

The **Omega Vac** is made from a high-impact Diamond ABS Polymer for more durability and longer life. It comes complete with all accessories listed above which are also statically conductive for maximum static protection. It also features field replaceable latches and an economical by-pass motor ideal for the recycle industry.

## Omega Vac Models

PART NUMBER

OMEGA VAC WITH STANDARD .3 MICRON FILTER (120 v)	<b>VACOMEGA</b>
OMEGA VAC WITH HEPA FILTER (120 v)	<b>VACOMEGACT</b>
OMEGA VAC WITH STANDARD .3 MICRON FILTER (230 v)	<b>VACOMEGA220</b>

## Omega Vac REPLACEMENT PARTS (FOR ALL MODELS)

Vacuum Hose 6 foot	<b>31661</b>
Vacuum Hose 10 foot	<b>31671</b>
Power Cord (120 volt only)	<b>31651</b>
Crevice Tool	<b>31654</b>
Crevice Tool Brush	<b>31652</b>
16" Rubber Flex Neck	<b>31657</b>
HEPA Filter (.3 @ 99.97% Efficiency Micron Retention)	<b>OF612HE</b>
ULPA Filter (99.999% efficient at .12 microns)	<b>OF712UL</b>
Standard Filter (.3 Micron Retention)	<b>31700</b>

**ATRIX INTERNATIONAL, INC.**

1350 Larc Industrial Blvd., Burnsville, MN 55337  
E-Mail: sriedel@atrix.com

(800) 222-6154

(952) 894-6154

Internet: www.atrix.com

(fax) (952) 894-6256