



Products	BV _{DSS} Min (V)	Configuration	R _{DS(ON)} Max. (Ohms) @ V _{GS} =				Q _g (nC) Typ @ V _{GS} = 5V (Note pg. i)	Maximum Rating	
			10V	4.5V	2.5V	1.8V		I _D (A)	P _D (W)
DIP-8 Complementary N- and P-Channel									
FQG4902	250 -250	Complementary	2	-	-	-	6	0.54	1.4
FQG4904	400 -400	Complementary	3	-	-	-	7.6	0.46	1.6
TO 220 N Channel									
ISL9N302AP3	30	Single	0.0025	0.0033	-	-	110	75	345
ISL9N303AP3	30	Single	0.0032	0.005	-	-	61	75	215
FDP8030L	30	Single	0.0035	0.0045	-	-	120	80	187
FDP7045L	30	Single	0.0045	0.006	-	-	50	100	125
ISL9N304AP3	30	Single	0.0045	0.0075	-	-	38	75	145
FDP6676	30	Single	0.006	0.0075	-	-	43	84	93
ISL9N306AP3	30	Single	0.006	0.0095	-	-	30	75	125
FDP6670AL	30	Single	0.0065	0.0085	-	-	24	80	68
FDP7030L	30	Single	0.007	0.01	-	-	35	100	125
ISL9N307AP3	30	Single	0.007	0.0115	-	-	28	75	100
FDP7042L	30	Single	0.0075	0.009	-	-	32	50	83
FDP7030BL	30	Single	0.009	0.012	-	-	23	60	65
ISL9N310AP3	30	Single	0.01	0.015	-	-	17	62	70
RFP70N03	30	Single	Use ISL9N310AP3						
FDP6035L	30	Single	0.011	0.019	-	-	34	58	75
ISL9N312AP3	30	Single	0.012	0.02	-	-	13	58	75
ISL9N316AP3	30	Single	Use ISL9N312AP3						
FDP6035AL	30	Single	0.0125	0.017	-	-	17	48	58
FDP6030L	30	Single	0.0135	0.02	-	-	34	52	75
FQP45N03L	30	Single	0.014	0.02	-	-	13	21	55
FDB6603AL	30	Single	Use FDP6030BL						
FDP6030BL	30	Single	0.018	0.024	-	-	12	40	60
HUF76009P3	30	Single	Use FDP6030BL						
HUF76107P3	30	Single	0.052	0.085	-	-	4.7	20	35
FDP6676S	30	SyncFET	0.0065	0.008	-	-	40	76	70
FDP6670S	30	SyncFET	0.0085	0.0105	-	-	23	62	62.5
FDP6644S	30	SyncFET	0.01	0.012	-	-	27	55	60
FDP6690S	30	SyncFET	0.0155	0.023	-	-	11	42	48
HUF75229P3	50	Single	0.022	-	-	-	35	44	90
BUZ11	50	Single	0.04	-	-	-	-	30	75
HUF75345P3	55	Single	0.007	-	-	-	125	75	325
HUFA75345P3	55	Single	0.007	-	-	-	125	75	325
HUF75344P3	55	Single	0.008	-	-	-	90	75	285
HUFA75344P3	55	Single	0.008	-	-	-	90	75	285
HUF75343P3	55	Single	0.009	-	-	-	92	75	270
HUFA75343P3	55	Single	0.009	-	-	-	92	75	270
HUF75339P3	55	Single	0.012	-	-	-	60	75	200
HUFA75339P3	55	Single	0.012	-	-	-	60	75	200
HUF75337P3	55	Single	0.014	-	-	-	51	75	175
HUFA75337P3	55	Single	0.014	-	-	-	51	75	175
HUF75333P3	55	Single	0.016	-	-	-	40	66	150
HUFA75333P3	55	Single	0.016	-	-	-	40	66	150
HUF75332P3	55	Single	0.019	-	-	-	40	60	145
HUFA75332P3	55	Single	0.019	-	-	-	40	60	145
HUFA75329P3	55	Single	0.024	-	-	-	35	49	128
HUF75329P3	55	Single	0.026	-	-	-	35	49	128
HUF75321P3	55	Single	0.034	-	-	-	21	35	93
HUFA75321P3	55	Single	0.034	-	-	-	21	35	93
HUF75309P3	55	Single	0.07	-	-	-	11	19	55
HUFA75309P3	55	Single	0.07	-	-	-	11	19	55