

## Infra-Red Heat Lamps

**PHILIPS**



Hard Blown (R125)



Hard Pressed (PAR38)

- Infra-red tungsten filament heat lamps in both R125 and PAR38 styles
- 5000 hours average life
- **Hard Blown** version (R125) resitant to thermal shocks, such as water splashes, making it suitable for industrial applications
- **Hard Pressed** versions have a high-efficiency reflector and refractor lens design, allowing accurate heat direction to where it is needed
- ES fitting
- Voltage: 240/250V

**New**

450602

Type	Watts	Order Code	+	Price Each	+
Hard Blown	250W	130-3431 ●	--	--	--
Hard Pressed	100W	130-3432 ●	--	--	--
Hard Pressed	175W	130-3433 ●	--	--	--