

## Temperature Controlled - W Series

200 Watt, W201 and W201E Barrel length (excl tip) = 131, Barrel dia = 18

100 Watt, W101 and W101E Barrel length (excl tip) = 96, Barrel dia = 15

60 Watt, W61 and W61E Barrel length (excl tip) = 75, Barrel dia = 11

- Well balanced lightweight irons
- High thermal reserve
- Temperature determined by tip selection
- Thermoplastic handle
- Capacitor is incorporated to improve switch life and prevent interference
- Fully earthed
- Fitted with 1.5m burn-proof lead
- Suitable for use with transistors, PCBs, heavy electrical connections and even sheet metal

		Mfrs.		Price Each			
Wattage	Voltage	List No.	Order Code	+	+	+	+
60 W	240 V	W61 UK	415-807				
60 W	120 V	W61E	415-819				
100 W	240 V	W101 UK	415-820				
100 W	120 V	W101E	415-832				
200 W	240 V	W201D	415-844				
200 W	120 V	W201E	415-856				
Irons with Euro Schuko Plug							
60 W	240 V	W61 EU	800-650				
100 W	240 V	W101 EU	800-661				
200 W	240 V	W201	800-673				