

CB-Amateur Radio Coaxial Cable — Low-Loss Foam RG-58 A/U and 8/U Types— Both 50 ohm Military-Type Braid Coverage

Individually packaged and fitted with PL-259 connectors on both ends. These cables are designed to be used with two-way systems, such as Citizens Band (CB), Commercial, Amateur, and Marine equipment applications. They provide a positive link between the transmitter and antenna or between the receiver and antenna.

The foam RG-58A/U Type is smaller in size (.195 O.D.) and well suited to mobile unit applications where greater flexibility is called for. The foam RG-8/U Type is larger (.405 O.D.) and capable of handling higher power requirements with lower signal losses. Black PVC jacket.

Description UL AWM Style	Trade No. UL NEC Type CSA Cert.	Length		Standard Unit Lbs. ea.	Cable Type
		ft.	m		
	9349	3	0.91	.1	58A/U Foam
	9350	15	4.57	.6	58A/U Foam
	9352	50	15.24	1.5	58A/U Foam
	9354	50	15.24	5.5	8/U Foam
	9355	75	22.86	8.3	8/U Foam

High-Voltage Leads