

Product Datasheet

2470PJI050P40

EAN 4031582010053

Swivel caster, Housing made of pressed steel, zinc-chromatised, double ball bearing swivel head, axle riveted, Wheel centre made of Polypropylene, Tread: TENTEprene (thermoplastic rubber), grey non-marking, plain bearing

Wheel diameter	2 "
Width of Tread	0.75 "
Size of Plate	2.36 x 2.36 "
Plate hole centres	1.89 / 1.5 x 1.89 / 1.5 "
Plate hole	0.24 "
Offset	0.98 "
Swivel Interference	3.94 "
Overall height	2.72 "
Dynamic Load capacity	110 LBS
Static Load capacity	220 LBS
Temperature	-4 / 140 °F
Standard	EN 12530
Weight	0.353 LBS



Versions:

