06.63.206

Detailed View



06.63.206 Locking Support, Threaded Female

Length 20,0 mm

Material Nylon 66

Thread Typ M3

Dia. Hole Board 4,0 mm

Dia. Hole Chassis 3,2 mm

Typ Support Threaded Male

UL-Flamability UL94 HB Board Thickness 2,10 mm


Model Support Treaded Female

Colour black

Design Screw Mounting

RoHS konform / WEEE konform / 76/769/EWG konform / PAKs frei

Locking Su





Length Material Thread Typ

Dia. Hole Board	4,0 mm
Dia. Hole Chassis	3,2 mm
Тур	Support Thread
UL-Flamability	UL94 HB
Board Thickness	2,10 mm
Model	Support Treade
Colour	black
Design	Screw Mounting
	RoHS konform
Specifications	<u>Details</u>
Deliverydate	from stock
Price Grading	100 to 499 piec
	500 to 999 piec
	1000 to 2499 p
	more than 2500

To order

