

Metric

DIN 338/BS 328

Flute geometry Standard helix, right hand spiral Point angle 118 Surface treatment Bright: below 1.3mm Blue: above 1.3mm Application General purpose engineering drills.

Size	Flutelength(mm)	Overalllength(mm)	Order code	Priceeach
0.30	3	19	22-3050B	.
0.35	4	19	02-0003	.
0.40	5	20	22-3054	.
0.45	5	20	22-3056	.
0.50	6	22	22-3058	.
0.55	7	24	22-3060	.
0.58	7	24	22-3061	.
0.60	7	24	22-3062B	.
0.65	8	26	22-3067	.
0.68	9	28	22-3069	.
0.70	9	28	22-3068	.
0.75	9	28	02-3069	.
0.78	10	30	22-3071	.
0.80	10	30	02-3070	.
0.85	10	30	02-3071	.
0.90	11	32	02-3072	.
0.95	11	32	02-3073	.
1.00	12	34	02-3074	.
1.05	12	34	02-3075	.
1.10	14	36	02-3076	.
1.15	14	36	02-3077	.
1.20	16	38	02-3078	.
1.25	16	38	02-3079	.
1.30	16	38	02-3080	.
1.35	18	40	02-3081	.
1.40	18	40	02-3082	.
1.45	18	40	02-3083	.
1.50	18	40	02-3084	.
1.55	20	43	02-3085	.
1.60	20	43	02-3086	.
1.65	20	43	02-3087	.
1.70	20	43	02-3088	.
1.75	22	46	02-3089	.
1.80	22	46	02-3090	.
1.85	22	46	02-3091	.
1.90	22	46	02-3092	.
1.95	24	49	02-3093	.
2.00	24	49	02-3094	.
2.05	24	49	02-3095	.
2.10	24	49	02-3096	.
2.15	27	53	02-3097	.
2.20	27	53	02-3098	.
2.25	27	53	02-3099	.
2.30	27	53	02-3100	.
2.35	27	53	02-3101	.
2.40	30	57	02-3102	.
2.45	30	57	02-3103	.
2.50	30	57	02-3104	.
2.55	30	57	02-3105	.
2.60	30	57	02-3106	.
2.65	30	57	02-3107	.

2.70	33	61	02-3108	.
2.75	33	61	02-3109	.
2.80	33	61	02-3110	.
2.85	33	61	02-3111	.
2.90	33	61	02-3112	.
2.95	33	61	02-3113	.
3.00	33	61	02-3114	.
3.10	36	65	02-3115	.
3.20	36	65	02-3116	.
3.25	36	65	22-3077	.
3.30	36	65	02-3117	.
3.40	39	70	02-3118	.
3.50	39	70	02-3119	.
3.60	39	70	02-3120	.
3.70	39	70	02-3121	.
3.80	43	75	02-3122	.
3.90	43	75	02-3123	.
4.00	43	75	02-3124	.
4.10	43	75	02-3125	.
4.20	43	75	02-3126	.
4.30	47	80	02-3127	.
4.40	47	80	02-3128	.
4.50	47	80	02-3129	.
4.60	47	80	02-3130	.
4.70	47	80	02-3131	.
4.80	52	86	02-3132	.
4.90	52	86	02-3133	.
5.00	52	86	02-3134	.
5.10	52	86	02-3606	.
5.20	52	86	02-3607	.
5.30	52	86	02-3608	.
5.40	57	93	02-3609	.
5.50	57	93	02-3610	.
5.60	57	93	02-3611	.
5.70	57	93	02-3612	.
5.80	57	93	02-3613	.
5.90	57	93	02-3614	.
6.00	57	93	02-3615	.
6.10	63	101	02-3616	.
6.20	63	101	02-3617	.
6.30	63	101	02-3618	.
6.40	63	101	02-3619	.
6.50	63	101	02-3620	.
6.60	63	101	02-3621	.
6.70	63	101	02-3622	.
6.80	69	109	02-3623	.
6.90	69	109	02-3624	.
7.00	69	109	02-3625	.
7.10	69	109	02-3626	.
7.20	69	109	02-3627	.
7.30	69	109	02-3628	.
7.40	69	109	02-3629	.
7.50	69	109	02-3630	.
7.60	75	117	02-3631	.
7.70	75	117	02-3632	.
7.80	75	117	02-3633	.

7.90	75	117	02-3634	.
8.00	75	117	02-3635	.
8.10	75	117	02-3636	.
8.20	75	117	02-3637	.
8.30	75	117	02-3638	.
8.40	75	117	02-3639	.
8.50	75	117	02-3640	.
8.60	81	125	02-3641	.
8.70	81	125	02-3642	.
8.80	81	125	02-3643	.
8.90	81	125	02-3644	.
9.00	81	125	02-3645	.
9.10	81	125	02-3646	.
9.20	81	125	02-3647	.
9.30	81	125	02-3648	.
9.40	81	125	02-3649	.
9.50	81	125	02-3650	.
9.60	87	133	02-3651	.
9.70	87	133	02-3652	.
9.80	87	133	02-3653	.
9.90	87	133	02-3654	.
10.00	87	133	02-3655	.
10.10	87	133	22-3102	.
10.20	87	133	22-3103	.
10.30	87	133	22-3108	.
10.40	87	133	22-3109	.
10.50	87	133	02-3656	.
10.60	87	133	22-3110	.
10.70	94	142	22-3111	.
10.80	94	142	22-3113	.
10.90	94	142	22-3114	.
11.00	94	142	02-3657	.
11.10	94	142	22-3115	.
11.20	94	142	22-3116B	.
11.30	94	142	22-3118	.
11.40	94	142	22-3119	.
11.50	94	142	02-3658	.
11.60	94	142	22-3120	.
11.70	94	142	22-3121	.
11.80	94	142	22-3123	.
11.90	101	151	22-3124	.
12.00	101	151	02-3659	.
12.10	101	151	22-3127	.
12.20	101	151	22-3128B	.
12.30	101	151	22-3130B	.
12.40	101	151	22-3131	.
12.50	101	151	02-3660	.
12.60	101	151	22-3132	.
12.70	101	151	22-3133	.
12.80	101	151	22-3135	.
12.90	101	151	22-3138	.
13.00	101	151	02-3661	.
13.10	101	151	02-3662	.
13.20	101	151	02-3663	.
13.30	108	160	02-3664	.
13.40	108	160	02-3665	.

13.50	108	160	02-3666	.
14.00	108	160	02-3671	.
14.25	114	169	22-3139	.
14.50	114	169	22-3140	.
14.75	114	169	22-3142	.
15.00	114	169	02-3672	.
15.25	120	178	22-3144	.
15.50	120	178	22-3146	.
16.00	120	178	22-3150	.
16.50	125	184	22-3151	.
17.00	125	184	22-3152	.
17.50	130	191	22-3153B	.
18.00	130	191	22-3154	.
18.50	135	198	22-3155	.
19.00	135	198	22-3158	.
20.00	140	205	22-3157	.

CLOSE WINDOW