

Felxible magnetic strip

Roebuck



Pair of mating flexible magnetic strips, complete with adhesive backing. Maximum operating temperature 50 ° C.

517796

Width (mm)	Thickness (mm)	Length (mm)	Order code	Price each
9.5	3.6	150	No Order Code	