



NOTE: All relevant materials are complied with RoHS directive .

6	PLASTO-VISCO-ELASTIC BODY	4	M562
5	SCREW 3*6PWB	4	M805
4	METAL CASE, THICKNESS 0.8mm	1set	M415
3	UL1061 26AWG INSULATOR, LENGTH 150mm	47	M541
	MAIN HEART 2-16-2	1	M94
	SCREW 4*12.5mm WITH PAD	1set	M94
2	KNOB FOR A, B, SWITCH	1	M94
	HEX-NUT 4.75*13mm, SCREW CAP 4.75*1.5	6set	M95
1	HD15 FEMALE, GOLD FLASH ON CONTACTS, BLUE INSULATOR	3	M108
No.	DESCRIPTION	QTY	Supplier
APPROVED			Cable Length Unless Other Spc
CHECKED	RAN		Tolerances 0 ±0.01M 0 ±0.2M 0.21~1.0M ±0.02M 1.1 ~1.5M ±0.025M 1.51~2.1M ±0.03M 2.1M ↑ ±0.04M
DRAWING	TIAN	ITEM NO.	SB-472