# DURACELL<sup>®</sup> Rechargeable



# **Easy Charger CEF24**



#### **DESIGN**

International Charge Capability — device can be used worldwide (with suitable converter plug)

Primary plug matches local requirements

### **BENEFITS**

- Sleek and compact design
- Easy and convenient power
- Comes with 2 (AA or AAA) Duracell Standard cells

## **FEATURES**

Single charging channel

- Charges 2 AA or 2 AAA
- Charge time: 8-10 hours

Bi-color charging status LED indicator

- Red = Charging
- Green = Complete
- Flashing Red = Error Abnormal battery or abnormal temperature

#### **SAFETY**

Microprocessor Controlled

- Charge Termination based on dV and built-in timer
- Primary Cell Detection will not charge non-rechargeable batteries
- Reverse Polarity Protection
- Over-temperature shut-off prevents overheat of cell
- Over-charge protection prevents cell damage

### **TECHNICAL**

Battery Charger Class 2, Integral Power Supply

Plug Direct Plug-In Matches Local Requirements

Battery Type NiMH HR6 AA or HR03 AAA
Battery Fit 2 NiMH AA/HR6 or 2 AAA/HR03

Product Weight 67 grams

Input 100-240V AC, 50-60 Hz

Output HR6/AA: 300 mA / HR03/AAA: 140 mA

Operating Temperature 0 ° C - 40 ° C

Product Dimensions 105 (L) x 50 (W) x 35 (H)

<sup>\*</sup>Charge rate and time is dependent on cell capacity, discharge state, and operating temperature.