

Bosch GSR 12v Cordless Drill Driver GSR122



Features:

- Compact and handy for work in tight spaces and overhead
- Quick, one-handed tool changes thanks to single-sleeve quick-change chuck with Auto Lock
- Best handling thanks to Softgrip on slim pistol grip and sensitive electronic switch
- High-grade planetary gear with smooth-running, dustproof switch system between 1st and 2nd gear
- Fully functional even after a 2-m drop onto concrete thanks to the new housing concept
- 15 torque settings + drill setting
- Run-out brake
- Forward/reverse rotation
- Switch-on lock

Specifications:

Torque, max, hard screwdriving application: 32 Nm

Torque, max., soft screwdriving applications: 19 Nm

No-load speed, 1st gear: 0 /- 400 1/min

No-load speed, 2nd gear: 0 /- 1.200 1/min

Torque setting range, min. / max.: 1 /- 8 Nm

Drill spindle thread: 3/8 Zoll

Chuck jaw width, min./max.: 1 / 10 mm

Battery voltage: 12 V

Weight including battery, approx.: 1,70 kg

Quick change chucks: 10 mm

Charging time, approx.: 1 H

Torque settings: 15

Length: 228,0 mm

Height: 238,0 mm

Drilling diameter, Wood: 25,00 mm, Steel: 11,00 mm

Max. screw diameter: 7 mm