

Bosch GSR12-23 12 V Cordless Drill/Driver



Compact and lightweight, suitable for overhead working. Air cooling for long parts life.

- 2-speed
- 25 torque settings
- Softgrip
- Compact dimensions

- No-load speed, 1st gear: 0 - 400 rpm
- No-load speed, 2nd gear: 0 - 1.200 rpm
- Torque, max. (soft screwdriving applications): 11 Nm
- Torque, max. (hard screwdriving applications): 27 Nm
- Chuck jaw width, min./max.: 1 / 10 mm
- Battery type: NiCd
- Battery voltage: 12 V
- Battery capacity: 1,5 Ah
- Charging time, approx.: 60 min
- Max. screw diameter: 7 mm (0.27")