

DATA SHEET



PART NO: T 3489ST

ISSUE NO: 1

CATALOGUE NO: AD-0500300REU2.1

CUSTOMER NO: N/A

DESCRIPTION 5Vdc Regulated 300mA Euro Plugtop Adaptor



INPUT VOLTS	230Vac
FREQUENCY	50Hz
MAG CURRENT (max.)	50mA
O/P VOLTS NO LOAD	
O/P VOLTS	5.1Vdc
O/P CURRENT	
O/P VOLTS	5Vdc
O/P CURRENT	300mA
FLASH TEST	3.75KV
OUTPUT CONNECTOR	6 Way
OUTPUT POLARITY	Either
LEAD LENGTH	1.8mtr
APPROVALS	N/A
LENGTH	78.6mm
DEPTH	43.9mm
WIDTH	52.7mm
WEIGHT	330 grams

LABELLING:

AC-DC ADAPTOR
 MODEL NO:AD-0500300R
 INPUT :230VAC 50Hz 7W
 OUTPUT :5VDC 300mA 1.5VA
 STONTRONICS LIMITED

 CAUTION: DO NOT REMOVE COVER

MATERIAL : PVC SHEET
 BASE : BLACK COLOUR
 WORDS : WHITE COLOUR
 SIZE : 32.6 x 32.6mm

SCHEMATIC:

