

Robust Food Thermometer with Interchangeable Probes

You've always got one hand free





Exact measurements on arrival of the product with alarm if limits are exceeded



Special interchangeable measuring tips for frozen goods



Probe heads are easy to exchange



Three different measuring tips for different applications



The professional temperature measurement instrument for the food industry



Fast and convenient measurement during production



Special measuring tip for frozen goods

How you benefit

- 3 different measuring tips for various applications
- Measuring tip can be exchanged by the user
- 2 freely adjustable limit values, optical and acoustic alarm
- Built-in backlit display
- Acoustic key feedback
- · 2-line display
- Watertight (IP 65) and robust
- Ergonomic shape



Robust food thermometer with interchangeable probe tips

The professional temperature measurement instrument for the food industry

The testo 105 thermometer with interchangeable measuring tips for different applications was developed with the help of practitioners in the food industry. One thermometer - three areas of application.

Its ergonomic shape and the high-up display make the testo 105 ideal for use in production, incoming goods inspections and for frequent repetitive measurements. The backlit display can be read easily even under poor light

The user can set an upper and lower limit so that an optical or acoustic alarm is given if critical thresholds are exceeded.

Technical Data Instrument testo 105 °C/°F Parameter NTC Measuring sensor 1 channel (internal) No. of meas. channels Meas. range -50 to +275 °C 0.1 °C Resolution Accuracy ± 1 °C or (-50 to -20.1 °C) ± 1% (100.1 to 275 °C) ± 1 digit ± 0.5 °C (-20 to 100 °C) Display LCD, 1-line Plug-in NTC probe head Sensor Standard (t99 < 15 s) Length 120 mm Frozen goods (t99 < 60 s) Length 90 mm Long (t99 < 15 s) Length 200 mm 2 measurements Measuring rate per second Operation temperature -20 °C to +50 °C -40 °C to +70 °C Storage temperature 4x lithium Battery type button cell LR44 Battery life 80 h (Auto Off 10 Min) Housing ABS with soft coating in handle area, protection class IP 65 Dimensions 145 x 38 x 195 mm Weight

Complete case for field use

In addition to the testo 105 instrument, the high-grade aluminum case also contains the two measuring tips (② for frozen goods and ③ for large items).

Set contains

- testo 105 with standard measuring tip (120 mm)
- Frozen goods measuring tip
- Long penetration measuring tip (200 mm)
- Instruction manual
- Batteries

Quick Order Fax



Qty.	Item	Order no.	
	One-hand thermometer with penetration tip, frozen goods tip, long measuring tip, wall bracket in aluminum case	0563 1052	
	One-hand thermometer with penetration tip	0563 1051	
	Penetration tip for testo 105, length 100 mm (1)	0613 1051	
	Frozen goods tip for testo 105 (2)	0613 1052	
	Long measuring tip for testo 105, length 200 mm (3)	0613 1053	
	Aluminum case for one-hand testo 105 thermometer and accessories	0554 1051	

Item		
Name	Address	
Company		
Telephone/fax	E-mail	
Department	Signature	