



product details

72631

Product description: 72631
 EAN/ Product: 4050300859187
 Quantity: Folding carton box (FS) contains 1 Piece (PCE)

You can find this product in the eCatalog:
http://catalog.myosram.com?~language=EN&~country=COM&it_p=4050300859187

Suitable for strip lighting configuratio	No
--	----

Applications	
Holder designation	G5
Protection class IK (shock resistance)	IK07
Protection class	I
Accessories	PENDANT KIT (4050300792200); LOUVRE (4008321079909)
Type of connection	FIXED CONNECTION (TERMINAL)
IP code	IP20
Protection against ignition and fire	F, MM
Luminaire efficiency	0.84

General Description	
Body material	STEEL
Recycling	Yes
Number of lighting outlets	1
Sstl-Number	4030731
Energy Label - EEI	A2
Equipped with lamp	Yes
Standards	CE; ENEC10 VDE
Equipment	FQ 39W/840 HO

Technical - Colors	
Color of the luminaire	WHITE

Technical - Electrical Data	
Nominal wattage	39 W
Operating mode	ELECTRONIC CONTROL GEAR (ECG) (QTI)
Nominal voltage	230-240 V
Mains frequency	50-60 Hz

Technical - Geometries	
Length	884 mm
Cable penetration	478 mm
Mounting hole spacing, length	838 mm
Width	38 mm
Height	58 mm

Technical - Light Technical Data	
Color rendering index Ra	80...89
Color temperature	4000 K
Luminous flux	3100 lm



31.08.2010

Subject to change without notice. Errors and omission excepted.
 © 2010 OSRAM GmbH

Page 1 from 2



product details

72631

Technical - Temperatures

Glow Wire Test according to IEC 695-2-1 960 °C

Packaging units

EAN	Packaging type and content	Dimensions in h x w x l	Gross weight	Volume
4050300859187	Folding carton box contains 1 Piece	73,000 mm x 50,000 mm x 896,000 mm	1.119,000 g (0,000 g)	3,270 Cubic dec.
4050300859194	Shipping carton box contains 4 Piece	146,000 mm x 107,000 mm x 908,000 mm	4.751,000 g (0,000 g)	14,185 Cubic dec.

OSRAM ECOPACK-FQ

OSRAM ECOPACK-FQ luminaires are extremely bright. Thanks to 16 mm LUMILUX T5 HO fluorescent lamps, they provide up to 50% greater luminous flux than batten luminaires of the same length equipped with 26 mm fluorescent lamps.

- Compact electronic batten luminaire for fixed connections
- With QUICKTRONIC QT_i Electronic Control Gear
- Long lamp life, thanks to cut-off technology
- Without cover for maximum luminous flux
- Equipped with innovative LUMILUX T5 HO 840 fluorescent lamp
- CE Sign ENEC 10 Sign VDE Sign F Sign MM Sign Protection class 1 sign IP20, Glow wire test at 960 °C, IK07, Light color 840, 230-240 V, 50-60 Hz, G5 base.