
DURACELL®


Zinc Air Battery

13



Nominal Voltage:	1.4 V
Rated Capacity:	290 mAh at 1500 ohm to 1.1 V at 21°C (70°F)
Nominal Internal Impedance:	7.5 ohm @ 1kHz
Average Weight:	0.8 gm
Volume:	0.26 cm ³
Terminals:	Flat
Operating Temperature Range:	0°C to 50°C (32°F to 122°F)
ANSI: IEC:	7000 ZD PR48

Typical Discharge Characteristics at 21°C (70°F)



^{*} Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy / service life that the battery will provide for various load conditions.