

**Enclosure
KLIPPON K41****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com



For many years, the name Klippon has stood for competence and quality in enclosures and customer-specific, connection-ready applications. Customer satisfaction is our number one priority. That is why we have updated and modernized our line of aluminium housings. These are improved products for all application requirements.

General ordering data

Order No.	1565270000
Part designation	KLIPPON K41
Version	Enclosures, 120 mm, 81 mm, 122 mm, Aluminium AISi12
GTIN (EAN)	4008190184636
Qty.	1 pc(s).

Enclosure KLIPPON K41

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-2083
 www.weidmueller.com

Technical data

Dimensions (1)

Weight	840 g	Length	81 mm
Width	122 mm	Height	120 mm
Fixing dimension, width	106 mm		

General information

Fixing dimension, width	106 mm	Material	Aluminium AISi12
Surface	untreated	Cover fixing	M4 torx stainless steel screws with slot
Enclosure fixing	Holes 4 mm	Integral fixing	threaded holes M6
Material	Aluminium AISi12	Resistance to shocks	10.00 J
Sealing material	Neoprene	Surface	untreated

Cable glands top/bottom

M 12	6	M 16	6
M20	3	M25	2
M32	1	Side of enclosure	left right

cable glands, left

M 12 (3)	4	M 20 (3)	2
----------	---	----------	---

cable glands, right

M 12 (2)	4	M 16 (2)	4
M 20 (2)	2	M 25 (2)	1
M 32 (2)	1	Side of enclosure	left right

horizontal assembly

WDU 10 / ZDU 10	1x6	WDU 2,5 / ZDU 2,5 / IDU 2,5	1x13
WDU 4 / ZDU 4	1x11	WDU 6 / ZDU 6	1x8

vertical assembly

WDU 2,5 / ZDU 2,5 / IDU 2,5 (2)	*		
---------------------------------	---	--	--

Approvals

Approvals institutes	CULUS; GERMLLOYD; GOSTME25; MARITREG
----------------------	---

Classifications

eClass 5.1	27-14-91-07	eClass 6.0	27-14-91-07
------------	-------------	------------	-------------