

**Enclosure
KLIPPON K52****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com



For many years, the name Klippon has stood for competence and quality in enclosures and customer-specific, connection-ready applications. Customer satisfaction is our number one priority. That is why we have updated and modernized our line of aluminium housings. These are improved products for all application requirements.

General ordering data

Order No.	1565290000
Part designation	KLIPPON K52
Version	Enclosures, 160 mm, 91 mm, 160 mm, Aluminium AISi12
GTIN (EAN)	4008190030070
Qty.	1 pc(s).

**Enclosure
KLIPPON K52**

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com

Technical data

Dimensions (1)

Weight	1,480 g	Length	91 mm
Width	160 mm	Height	160 mm
Fixing dimension, width	140 mm		

General information

Fixing dimension, width	140 mm	Material	Aluminium AISi12
Surface	untreated	Cover fixing	M4 torx stainless steel screws with slot
Enclosure fixing	Holes 4 mm	Integral fixing	threaded holes M6
Material	Aluminium AISi12	Resistance to shocks	10.00 J
Sealing material	Neoprene	Surface	untreated

Cable glands top/bottom

M 12	14	M 16	8
M 40	1	M20	5
M25	3	M32	2
Side of enclosure	left right		

cable glands, left

M 12 (3)	8	M 20 (3)	3
----------	---	----------	---

cable glands, right

M 12 (2)	8	M 16 (2)	5
M 20 (2)	3	M 25 (2)	2
M 32 (2)	1	Side of enclosure	left right

horizontal assembly

WDU 10 / ZDU 10	1x9	WDU 2,5 / ZDU 2,5 / IDU 2,5	1x18
WDU 4 / ZDU 4	1x15	WDU 6 / ZDU 6	1x11

Approvals

Approvals institutes	CULUS; GERMLLOYD; GOSTME25; MARITREG
----------------------	---

Classifications

eClass 5.1	27-14-91-07	eClass 6.0	27-14-91-07
------------	-------------	------------	-------------