

**Enclosure
KLIPPON K71****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com



For many years, the name Klippon has stood for competence and quality in enclosures and customer-specific, connection-ready applications. Customer satisfaction is our number one priority. That is why we have updated and modernized our line of aluminium housings. These are improved products for all application requirements.

General ordering data

Order No.	0573700000
Part designation	KLIPPON K71
Version	Enclosures, 230 mm, 100 mm, 280 mm, Aluminium AlSi12
GTIN (EAN)	4008190051808
Qty.	1 pc(s).

Enclosure KLIPPON K71

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Technical data

Dimensions (1)

Weight	2,925 g	Length	100 mm
Width	280 mm	Height	230 mm
Fixing dimension, width	260 mm		

General information

Fixing dimension, width	260 mm	Material	Aluminium AlSi12
Surface	untreated	Cover fixing	M4 torx stainless steel screws with slot
Enclosure fixing	Holes 4 mm	Integral fixing	threaded holes M6
Material	Aluminium AlSi12	Resistance to shocks	10.00 J
Sealing material	Neoprene	Surface	untreated

Cable glands top/bottom

M 12	42	M 16	30
M 40	4	M 50	3
M20	21	M25	12
M32	10	Side of enclosure	left right

cable glands, left

M 12 (3)	28	M 20 (3)	10
----------	----	----------	----

cable glands, right

M 12 (2)	28	M 16 (2)	18
M 20 (2)	10	M 25 (2)	8
M 32 (2)	3	M 40 (2)	2
M 50 (2)	2	Side of enclosure	left right

horizontal assembly

WDU 10 / ZDU 10	2x21	WDU 2,5 / ZDU 2,5 / IDU 2,5	2x42
WDU 4 / ZDU 4	2x35	WDU 6 / ZDU 6	2x26

Approvals

Approvals institutes	CULUS; GERMLLOYD; GOSTME25; MARITREG
----------------------	---

Classifications

eClass 5.1	27-14-91-07	eClass 6.0	27-14-91-07
------------	-------------	------------	-------------