

MV8132

Attribute		Value	UOM
Number of Colors		Single	
Source	Color	Red (AlGaAs)	
	Brightness	Standard	
Forward Voltage (V _F)	TYP	1.7	V
	MAX	2.4	V
Peak Wavelength		660	nm
Luminous Intensity (I _v)	MIN	630	mcd
	TYP	940	mcd
Package		T-1 3/4	
Lens	Diffusivity	Water Clear	
Viewing Angle		30	deg
Forward Current		40	mA
Spectral Line Half Width		20	nm
Peak Current		200	mA
Power Dissipation		110	mW