



GREENLEE®

A Textron Company

MADE FOR THE TRADE!™

COMMUNICATION TOOLS

2010 NEW PRODUCTS

Paladin Tools®

Paladin Tools®

Greenlee has redesigned some of our best selling Paladin Tools® products and made them better with increased functionality, higher performance, and updated styling. We've added new capabilities to our tools to employ industry trends, like terminating

"snagless" RJ45 plugs to crimping "mini" style compression connectors. Our

All-In-One Data/Phone Tool



Improved Dual-Durometer ProGrips for Improved Comfort and Control.

Crimps Snagless RJ45 Connectors as well as WE/SS RJ45, RJ11 & RJ22 Connectors. Patent Pending.

DataComm Snips



Stripping Cavities Integrated into Snipper Blade

Serrated Blade Prevents Wire Slipping

Patent-Pending Handle for Better Comfort and Leverage

redesigned tool handles provide increased comfort, reduce fatigue and improve the grip. And to further address our customers' growing needs, we've

expanded our lines with several new products including cutters, strippers and crimpers for UTP, Coax, Telco and Electrical applications.

All designed to make your job faster, safer, and easier.

MADE FOR THE TRADE!™

PowerPlay® GripPack



GripPack Pouch Can Hold PowerPlay® Tool in Both Open and Closed Positions



Includes PT-540



Select Paladin Tools® are covered by our Limited Lifetime Warranty.

ALL NEW PRODUCTS FROM **Paladin Tools**...

Cutters/Strippers

GripP-Strippers 10 & 20

- Head of tool and handles designed at optimum 22° angle to prevent awkward wrist bends.
- Spring-loaded open. Lock keeps tool closed.
- Features screw cutter and wire loops embedded in frames.



Improved dual-durometer ProGrips for improved comfort and control

Flat Cable Cutter

- Cut flat satin cables easily and quickly.
- Gripping pliers at tip of tool.



Improved dual-durometer ProGrips for improved comfort and control

CAT. NO.	DESCRIPTION
PA1117	GripP 10 cutter/stripper (22-10 AWG/.34-6 mm2)
PA1118	GripP 20 cutter/stripper (30-20 AWG/.05-.5 mm2)
PA1123	Wire Stripper Bundle, includes both PA1117 and PA1118

CAT. NO.	DESCRIPTION
PA1181	ProGrip Flat Cable Cutter for Flat Ribbon Cable up to 1.25"

Fiber Optic Strippers

ProGrip 3-in-1 Fiber Optic Stripper

- Precision CNC ground stripping cavities for:
 - 2.0 mm outer jacket
 - 900 µm buffer insulation
 - 250 µm buffer/acrylate
- Factory calibrated.



Combines three common fiber strip applications into one cost effective tool. Also features new dual-durometer ProGrips for improved control.

ProGrip 5-in-1 Fiber Optic Stripper

- Precision ground stripping cavities for:
 - 2.0 - 2.4 mm outer jacket
 - 2.0 - 3.0 mm loose tube
 - 2.8 - 3.0 mm outer jacket
 - 900 µm buffer insulation
 - 900/125 µm and 250/125 µm buffer/acrylate
- Factory calibrated.



Improved version of the PA1163 FiBerOptic with gripping plier removed to improve precision of strips. Also features new dual-durometer ProGrips for improved control.

CAT. NO.	DESCRIPTION
PA1177	ProGrip 3-in-1 Fiber Optic Stripper

CAT. NO.	DESCRIPTION
PA1171	ProGrip 5-in-1 Fiber Optic Stripper

Cable Cutters

Dual-Contour Round Cable Cutter

- Cuts solid or stranded cable up to AWG 6.
- Precise and effortless cuts.
- Round cutting minimizes cable deforming.
- Optimized for 4pair UTP and RG58, RG59, RG6/RG6Q Coax.



Upgraded 900265 (KT 8) with dual-durometer ProGrips and the same effortless cuts.

Contour Round Cable Cutter

- Cuts solid or stranded cable up to AWG 6.
- Precise and effortless cuts.
- Round cutting minimizes cable deforming.
- Optimized for 25pair UTP, RG7/RG11 Coax.



New version features a single blade contour for larger round cable.

CAT. NO.	DESCRIPTION
PA1179	Dual-Contour Round Cable Cutter

CAT. NO.	DESCRIPTION
PA1175	Contour Round Cable Cutter

THE BEST JUST GOT BETTER.

DataComm Cutters

DataComm Snips

- Serrated blade prevents wire slipping.
- Notches for stripping wires.
- Ergonomic design for the professional user.



Features patent-pending handle for greater comfort and control. GripPack compatible.

CAT. NO.	DESCRIPTION
PA1931	DataComm Snips

DataComm Snips & Knife Kit

- Leather pouch slotted to fit 2" (51 mm) belts.
- DataComm scissors feature an ergonomic design for the professional user.
- Utility knife has a full-size, no-slip textured handle.
- Knife designed to stay sharp and fit comfortably in your hand.



Features the PA1931 snips, the new PA1932 Cable Knife and a new black leather pouch embossed with the Paladin Tools® logo.

CAT. NO.	DESCRIPTION
PA1933	DataComm Snips & Knife Kit

DataComm Crimpers

All-in-One UTP Snagless Crimper

- Cuts and strips round or flat cable.
- For standard and "snagless" RJ45 connectors.
- Also crimps RJ11/22 and RJ22 WE/SS style plugs.



SNAGLESS RJ45



A further upgraded PA1556, this patent-pending new tool works with Snagless RJ45 plugs and features the new ProGrip dual-durometer handles.



*Crimper only

CAT. NO.	DESCRIPTION
PA1561	All-in-One UTP Snagless Crimper
PA9588	Snagless RJ45 Plugs - 10 Pack
PA9589	Snagless RJ45 Plugs - 40 Pack

SealTite® ProM Coax Crimper

- Crimps weatherproof linear CATV "F", BNC, RCA & right-angle compression-type connectors from all manufacturers.
- The only tool with a single, reversible head eliminating need for adapters.



Our top-selling adjustable compression tool (PA1555) upgraded to handle mini connectors and with ProGrips.



CAT. NO.	DESCRIPTION
PA1559	SealTite® ProM Coax Crimper

Electronic Crimpers

Electrical Terminal Crimper

- D-sub Pins & Sockets 26-28 AWG.
- Butt-Insulated Connectors 22-26 AWG.
- Telephone Piercing Spade Lugs 22-26 AWG.
- Open Barrel Connectors 14-18, 20-22 AWG.



Improved dual-durometer ProGrips for improved comfort and control.



CAT. NO.	DESCRIPTION
PA1176	Multi-Purpose Electrical Terminal Crimper

D-sub Indent Crimpers

- Adjustable Pin Height Locator.
- PA1460: 26-20 AWG (0.14-0.50 mm²)
- PA1461: 20-12 AWG (0.50-4.0 mm²)
- PA1462: 26-20 AWG (0.14-0.50 mm²)



Upgraded existing crimpers with dual-durometer ProGrips and internal improvements for greater reliability and precision.



CAT. NO.	DESCRIPTION
PA1460	D-sub 4 Indent Crimper 26-20 AWG
PA1461	D-sub 4 Indent Crimper 20-12 AWG
PA1462	D-sub 8 Indent Crimper 26-20 AWG

Telecom Crimpers

Telecom Splice Crimper

- Side cutter for AWG 19-26 copper.
- Non-slip grips for precision control.
- Crimp capacity:
 - UR: AWG 19-26
 - UY: AWG 22-26
 - UG: AWG 19-26



Features spring-loading and non-slip grips for easy handling.

CAT. NO.	DESCRIPTION
PA1178	Telecom Splice Crimper for button-style UR, UY and UG splice connectors

4-in-1 Telecom Splice Crimper

- Stripping cavity for AWG 22 wire.
- Needle-nose with knurled surface for gripping, wrapping and looping.
- Crimps UR, UY and UG Connectors.
- Non-slip grips for precision control.
- Side cutter for AWG 19-26 copper.



Needle-nose feature knurled gripping surface, perfect for wrapping and looping.

CAT. NO.	DESCRIPTION
PA1180	4-in-1 Telecom Splice Pliers for button-style UR, UY and UG splice connectors

GripPack Kits

PowerPlay® GripPack

- Includes PT-540 Multi-Tool, Hex Bit Adapter, DataComm Snips, Mini MagLite®, Sharpie® Marker.



All the tools you need to complement the PowerPlay®. Super-durable GripPack securely holds tools in place with swiveling quick release belt clip. Securely holds PT-540 tool open or closed.

CAT. NO.	DESCRIPTION
PA4945	GripPack PowerPlay® PT-540 Toolkit

GripPack UTP Essentials

- Includes SurePunch™ PDT with 110/66 Blade, DataComm Snips and Data SureStrip™ UTP Stripper.



Same quality and features as the original GripPack, in a trimmed down version.

CAT. NO.	DESCRIPTION
PA4946	GripPack Compact SurePunch™ Toolkit

Coax Tools

Coax Multi-Tool

- Combines three common coax prep functions in one tool:
 - Flaring tool for RG59 cables.
 - BNC Insertion holder.
 - Extraction tool for BNC connectors.



CAT. NO.	DESCRIPTION
PA1930	BNC Coax 3-in-1 Multi-Tool



GREENLEE®

A Textron Company

MADE FOR THE TRADE!™



NEED MORE INFORMATION?

Support: 800.272.8665

International Phone: +1.804.550.1121

Fax: 800.272.5257

International Fax: +1.804.550.0610

Website: www.paladin-tools.com

Email: customerservice@paladin-tools.com

www.paladin-tools.com



GREENLEE®

A Textron Company

www.greenlee.com MA-5527 6/10

4455 Boeing Drive • Rockford, IL 61109-2988 • USA • 815-397-7070

©2010 Greenlee Textron Inc. • An ISO 9001 Company • Printed in USA

Greenlee Textron Inc. is a subsidiary of Textron Inc.