

UT322


[Enlarge](#)
[Download Software](#)
[Download Manual](#)

Digital Thermometers

SPECIFICATIONS

Basic Functions	UT322
Temperature (K-Type) -200.0°C to +1372°C -328.0°F to +2501°F	✓
Temperature (J-Type) -210.0°C to +1200°C -346.0°F to +2192°F	✓
Temperature (T-Type) -250.0°C to +400.0°C -418.0°F to +752.0°F	✓
Temperature (E-Type) -150.0°C to +1000°C -238.0°F to +1832°F	✓
Temperature Best Accuracy	K,J,T,E-Type : 0.5% ± 0.8°C
Display Resolution	0.1°C (when > 999.9°C : 1°C)
T1, T2 input	✓
°C/°F/K Selection	✓
Data Logging	100
USB Data Transfer	✓
User Setup	✓
Temperature Data Hold	✓
Electricity Cut Off Memory	✓
MAX / MIN/ AVG temperatures	✓
Sleep Mode	✓
Low Battery Display	✓

GENERAL CHARACTERISTICS

Power	USB (Auto Double White Display Backlight) or 9V Battery (6F22)
LCD Size	30×32mm
Product Color	Red and Grey
Product Net Weight	270g
Product Size	175×85×30mm
Standard Accessories	Battery, English Manual, USB Cable, CD Software, K Type Temperature Probe
Standard Individual Packing	Gift Box
Standard Quantity Per Carton	40 pcs
Standard Carton Measurement	460x390x270mm (0.048 CBM Per Standard Carton)
Standard Carton Gross Weight	21kg

*Available at Extra Cost

Specifications and other information are subject to change without further notice.

[Back to main menu](#)