

UNIBOND NO MORE NAILS

Issue Date: 20-Feb-06

Ref: 10675TD

Identification:	A high strength adhesive for fixing most building materials. Water based & non-flammable. Manufactured by Henkel Consumer Adhesives.
Uses/Applications:	A high strength adhesive which eliminates the need for nails and screws in many DIY and repair jobs. Safe and easy to use, the solvent free paste forms an instant bond. Fills minor gaps in uneven surfaces.
Limitations/Misuse:	
Compliance with standards	Henkel Consumer Adhesives is certified by DQS (Certificate Registration number : 003052 QM/UM) as a company operating a Quality Management System to BS EN ISO 9001:2000, BS EN 14001 and OHSAS 18001.
Description:	
<i>Composition:</i>	Water based filled acrylic polymer.
Physical Properties:	
<i>Appearance:</i>	Smooth off white paste
<i>Odour:</i>	Very slight whilst wet.
Performance:	
<i>Fire:</i>	Non-flammable
<i>Water:</i>	Wet - water will disperse product.
<i>Chemicals:</i>	Resistant to petrol, oils, weak alkalis and dilute acids. Not resistant to strong acids and strong organic solvents.
<i>Biological:</i>	Contains a non-mercurial preservative and does not support the growth of bacteria or fungi.
<i>Thermal:</i>	Serviceable from -10°C to +50°C.
<i>Durability/Reliability:</i>	
<i>Compatibility with other products:</i>	Good adhesion to most building surfaces.
Working Characteristics:	
<i>Rheology:</i>	Easy spread viscous paste.
<i>Working time:</i>	Approximately 20 minutes, depending on temperature & relative humidity.
<i>Cure time:</i>	Approximately 24 hours, depending on temperature & relative humidity.
<i>Cure type:</i>	Water evaporation
<i>Temperature range:</i>	Do not apply below 10°C.
<i>Coverage:</i>	Approximately 11m using 6mm bead.
<i>Shelf life:</i>	At least 1 year in unopened cartridge.

Architect's Specification Clause

The adhesive to be used shall be UniBond No More Nails. It shall be used and applied strictly in accordance with the manufacturer instructions.

Health & Safety

This material is safe in normal use. However, with any material, good hygiene practices should be followed. DO NOT take internally. Keep out of eyes. Keep away from children & animals. Wash off skin with soap & water before it dries. People with sensitive skin should wear rubber gloves. THIS PRODUCT CONTAINS A FUNGICIDE.

FOR FULL DETAILS SEE SEPARATE HEALTH & SAFETY SHEET.

First Aid Procedure: See separate Henkel Health & Safety data sheet available on request

Emergency Action: See separate Henkel Health & Safety data sheet available on request

Supply

Prices & conditions of sale See separate Henkel price list available on request.

Packaging 12 cartridges per carton.

Advisory Service

For technical or practical advice on this or any other UniBond product please contact our technical services department on Winsford (01606) 593933. Fax: (01606) 863762.

Guarantee

The information supplied in our literature or given by our employees concerning the use of our products is based upon extensive experience and given in good faith in order to help you. We also warrant the consistent high quality of our products. However, as we have no control over site conditions or the execution of the work, we accept no liability for any loss or damage which may arise as a result thereof.