

DWG. NO. SD-5282-NA

E




D

C

B

A

DIMENSIONS IN METRIC DO NOT SCALE DRAWING



注記
NOTE

- 1 ウエハーのそりは、長さ 25.4 に対して0.24 MAX..
CAMBER MUST BE 0.24 MAX. PER 25.4
- △ 全極数が偶数の場合のみ適用。
TO BE APPLIED ONLY WHEN ALL CKTS. ARE EVEN.

34.48	30.48	10-33-1072	5282-07A	7
29.4	25.4	↑ -1062	↑ -06A	6
24.32	20.32	↑ -1052	↑ -05A	5
19.24	15.24	↑ -1042	↑ -04A	4
14.16	10.16	↓ -1032	↓ -03A	3
9.08	5.08	10-33-1022	5282-02A	2
B		A	EDP NO.	ENG. NO.

材料 MATERIAL		図中参照 SEE DRAWING		MOLEX-JAPAN CO.,LTD. 日本モレックス株式会社	
仕上げ FINISH		—		REVISE ONLY ON CAD SYSTEM	
適用電線範囲 WIRE RANGE		—		TITLE 名称 KK 5.08 WAFER ASS'Y WITH LOCK	
被覆外径 INS. RANGE		—		DRAWN BY '94/07/04 CHK'D BY '94/07/04 T.ASAKAWA Y.M.HIRAMOTO	
DRAWN BY '94/07/04		CHK'D BY '94/07/04		DWG. NO.	
APP'D BY '94/07/04		DATE		SCALE 4 : 1	
M.FUKUSHIMA		M.FUKUSHIMA		SD-5282-NA	
REV D		REV D		REV D	

角度 ANGLE	±3°		
30以上 OVER	+0.3		
10以上 30未満 OVER	+0.25		
10未満 UNDER	+0.2		
一般公差 GENERAL TOLERANCES		記号 LTR	変更内容 REVISION RECORD
		DR. CHK.	日付 DATE