

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY

MINNEAPOLIS, MINNESOTA

FED. MFR. CODE 91929

SWITCH - BASIC

CATALOG LISTING

BZ - 2RW84

BZ-2RW84
PAGE 1 OF 1

M

DRAWING
NUMBER

8

ISSUE

REPLACES

RELEASE NO.

CHECK

REVISIONS

A	CO	16736	GCH	17 MAY 62
B	CO	34306	KPK	4 JUN 75
C	CO	46304	JAP	13 OCT 79
D	CO	58037	SMA	1 OCT 85
E	CO	78874	DLT	18 NOV 94
F	CO	93346	DLT	11 SEP 98

CHECK

CHECK

CHECK

CHECK


CHECK

CHECK

CHECK

CHECK

CHECK



NOTE

△ MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS.

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE ----- 1 OZ MAX

RELEASE FORCE ----- 1/8 OZ MIN

DIFFERENTIAL TRAVEL ----- .007 - .050

OVERTRAVEL ----- .219 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT

S P D T

UNDERWRITERS' LAB. INC. LISTED RATING

-L96- 15 A - 125, 250, OR 480 VAC

1/2 A - 125 VDC; 1/4 A - 250 VDC

1/8 HP - 125 VAC; 1/4 HP - 250 VAC

-L288-

-L299-

-L306-



16A 250V

T85 5E4

SCALE FULL

DO NOT SCALE PRINT

UNLESS OTHERWISE SPECIFIED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE (.0) ± .030
TWO PLACE (.00) ± .015
THREE PLACE (.000) ± .005
ANGLES ±

WEIGHT .060 LB

FORMTEK

FO-50378

DRAWN

GCH

17 MAY 62