HUBER+SUHNER® DATA SHEET Coaxial Cable Connector: 16_MMCX-50-2-1/111_O

B

Description

Right angle cable plug for semi-rigid cable

Interface standards SUHNER-MMCX

Technical Data

Electrical Data

 $\begin{array}{ll} \text{Impedance} & \text{50 } \Omega \\ \text{Interface frequency max.} & \text{6 GHz} \end{array}$

Mechanical Data

Centre contact soldered
Outer contact soldered
Weight 0.0006 kg

Environmental Data

Operating Temperature -55 °C to 155 °C

Material Data

Piece PartsMaterialCentre contactBronzeOuter contactBrassBodyBrassInsulatorPFA / PTFE

Related Documents

Catalogue drawing DOU-00006007 Assembly instruction DOC-0000180777

Ordering Information

Single package 16_MMCX-50-2-1/111_OE Bulk 100 pcs package 16_MMCX-50-2-1/111_OH

Additional Information

Suitable cable EZ_86_TP_M17

Surface Plating

Gold Plating (Nickel underplated)

Gold Plating Gold Plating

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

Document: DOC-0000180778 J.00

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.

HUBER+SUHNER – Excellence in Connectivity Solutions

HUBER+SUHNER
HUBER+SUHNER AG

RF Technology 9100 Herisau, Switzerland Phone +41 (0)71 353 41 11 Fax +41 (0)71 353 45 90 www.hubersuhner.com

Page 1/1

Issued: 14.07.04 Uncontrolled Copy