

HUBER+SUHNER® DATA SHEET

Coaxial PCB Connector: 84_MMCX-50-0-1/111_O

Rev.: A



Description

Right angle PCB plug

Interface standards
SUHNER-MMCX



Technical Data

Electrical Data

Impedance 50 Ω
Interface frequency max. 6 GHz

Mechanical Data

Board mounting type through holes
Weight 0.0005 kg

Environmental Data

Operating Temperature -55 °C to 155 °C

Material Data

Piece Parts

Centre contact	Copper Beryllium Alloy
Outer contact	Brass
Body	Brass
Insulator	PFA / PTFE

Surface Plating

Gold Plating (Nickel underplated)
Gold Plating
Gold Plating

Related Documents

Outline drawing	DOU-00012883
Catalogue drawing	DCA-00012885
Mounting hole	DOU-00012639

Ordering Information

Bulk 100 pcs package	84_MMCX-50-0-1/111_OH
----------------------	-----------------------

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG
RF Technology
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 45 90
www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions