
Pomona®

Model 3231 Size B Aluminum Box With Cover BNC Male/Female



MATERIALS:

Connector: BNC (M) & BNC (F)

Body: Tarnish Resistant Plating, Center Contact: Male – Gold Plated Brass, Female – Gold Plated Beryllium Copper Solder Turret Terminal Screws: Steel

Shielded Housing: Die cast aluminum alloy 380 or 384.

Finish: Blue baked enamel per Fed. Std. 595 25109 over Phosphoric Etch

Cover: 1.02 (.040) thick aluminum #1100-H14

Finish: Clear anodized

Screws: 4 each #2-32 x 1/4". Pan head self-tapping. Steel.

RATINGS:

Operating Voltage: Inner conductor/Shield: 1000 VRMS Max. Operating Temperature: -55°C to +150°C Nominal Impedance: 50 Ohms

ORDERING INFORMATION: Model 3231

All dimensions are in inches. Tolerances (except noted): $.xx = \pm.02^{\circ}$ (,51 mm), $.xxx = \pm.005^{\circ}$ (,127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies. Made in USA

6/9/99	Sales: 800-490-2361 Fax: 888-403-3360
SY/EH/LS	Technical Assistance: 800-241-2060
S:\Engineering\Release\DataSheets\FlukeDataSheet\d3231_1_01.doc	