

Product Data Sheet



FP700-1D

artnr. 938141

Safety Products



Description: Two colour Basic harness for fall arrest only with sliding dorsal "D"ring.

Materials: 44mm Polyamide webbing
 Colour: Orange shoulderstraps / Green legstraps.
 Zinc plated-steel adjustment buckles.

Weight: 0,585 kg

Standards: EN361 / ANSI Z359.1 / CSA Z259.10

Performance Single size : Medium up to large.
 Length adjustable legstraps with quick buckles.

Packaging: polyethene bag

EN 361 - A body support for fall arrest purposes. The full body harness suitably arranged and assembled to support the whole body of a person and to restrain the wearer during and after the fall.

EN 361	Standard characteristics
<p>Full Body Harness</p>	<p>Characteristics</p> <p>Static tests</p>
Traction upwards 15 kN / (3min)	Test 1 Force and time of application
Traction downwards 10 kN / (3min)	Test 2 Force and time of application
4m	Dynamic tests Free fall
100 kg / 2m 1 Head up	Dummy and lanyard length Number and fall type
1 Head down	