

25

TERMINAL SPACING (5.0 ±1mm)

VOLTAGE

300

DIELECTRIC

LEAD SPACING

50

X7R

20

SPC-F004.DWG

ALL STATEMENTS

comp

mult

Multicomp Type #

During soldering or solvent cleaning.

Applications

Shows excellent stability to humidity and no change in capacitance over the full operating temperature range.



The internal electrodes are built inside the dielectric.

Small size, large capacity, suitable for taking place of aluminum electrolytic capacitors.

FEATURES:

Aging

Q. DF - DC voltage characteristic



SPC-F004.DWG

SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	TA-187	TA-187.DWG	A
SCALE:	NTS	U.O.M.: INCHES [mm]	SHEET: 2 OF 2