

**Features**

Product Description LiteOn LH-16D1P - DVD-ROM drive - IDE  
Device Type DVD-ROM drive  
Enclosure Type Internal  
Interface IDE  
Dimensions (WxDxH) 14.5 cm x 17 cm x 4.1 cm  
Weight 0.9 kg  
Optical Storage DVD-ROM - 5.25" x 1/2H  
Read Speed 48x (CD) / 16x (DVD)  
OS Required Microsoft Windows 2000, Microsoft Windows XP

**General**

Device Type DVD-ROM drive  
Enclosure Type Internal  
Interface IDE  
Width 14.5 cm  
Depth 17 cm  
Height 4.1 cm  
Weight 0.9 kg

**Optical Storage**

Type DVD-ROM - 5.25" x 1/2H  
Read Speed 48x (CD) / 16x (DVD)  
Supported CD Formats CD Extra, CD-DA (audio), CD-I, CD-ROM XA, Photo CD, Video CD, CD-ROM, CD+G (Karaoke CD)  
Supported Media Types CD-ROM, CD-R, CD-RW, DVD-ROM, DVD-R, DVD-RW, DVD+RW, DVD+R, DVD+R DL, DVD-R DL  
Media Load Type Tray  
Access Time 120 ms (CD), 140 ms (DVD)  
Buffer Size 2 MB  
Features SMART-X, Auto Balance System (ABS)  
Compliant Standards Video CD

**Expansion / Connectivity**

Interfaces 1 x IDE/ATAPI - 40 PIN IDC  
Compatible Bays 1 x front accessible - 5.25" x 1/2H

**Miscellaneous**

MTBF 70,000 hour(s)  
Package Type Retail

**Software / System Requirements**

OS Required Microsoft Windows 2000, Microsoft Windows XP  
System Requirements Details Pentium 4 - 1.3 GHz - RAM 128 MB - HD 650 MB

**Environmental Parameters**

Min Operating Temperature 5 °C  
Max Operating Temperature 45 °C  
Humidity Range Operating 15 - 80%