

Product Data Sheet



FP702-3D

artnr. 938145

Fall protection



Description: Two colour type harness with 3 anchorage points .Back anchorage (Lanyard with energy absorber, rope grab). Front anchorage (rope grab, rescue).

Materials: 44mm Polyamide webbing
Colour: Orange shoulderstraps / Green legstraps.
Zinc plated-steel adjustment buckles.

Weight: 0,750 kg

Standards: EN361 / ANSI Z359.1 / CSA Z259.10

Performance Length adjustable shoulderstraps.
Length adjustable legstraps with quick buckles.
Single Size: Medium up to X-large.

Packaging: polyethene bag

EN 361 - A body support for fall arrest purposes. The full body harness suitably arranged and assembled to support the whole body of a person and to restrain the wearer during and after the fall.

EN 361	Standard characteristics
<p>Full Body Harness</p>	<p>Characteristics</p> <p>Static tests</p>
Traction upwards 15 kN / (3min)	Test 1 Force and time of application
Traction downwards 10 kN / (3min)	Test 2 Force and time of application
4m	Dynamic tests Free fall
100 kg / 2m 1 Head up	Dummy and lanyard length Number and fall type
1 Head down	