

Convel 42000B DIN Rail Mounting Linear Power Supplies

The 42000B Series DIN rail mounting power supplies are supplied ready for connection. The unit has only to be snapped on to the 35mm profile rail (DIN 46277-3) and connected to the clearly marked terminal screws. A status LED indicates power OK.

For increased power two or more units may be connected in parallel. The output of these units is fully protected against short circuits and overload.



GENERAL SPECIFICATIONS

Input	115/230VAC 50/60Hz
D.C. Output	See Model Chart
Ripple & Noise	5mV PK-PK maximum
Output Voltage Tolerance	±0.5% maximum
Load Regulation	±0.05% for 50% load change
Line Regulation	±0.05% for 10% line change
Isolation: Input to Output	3750VAC minimum
Temperature Rating	Standard Range: 0°C to +40°C full-rated, derated linearly to 40% at 70°C
Safety	In accordance with EN609504
Case Size	l x w x h 162 x 105 x 98mm
Case Material	Steel housing with aluminium base
Weight	2.49kg

Model	Output Voltage Volts	Output Current Amps
42024B/3	24	3
42024B	24	4

Calex Electronics Limited

PO Box 2, Leighton Buzzard
Bedfordshire, England LU7 4AZ
Tel: +44(0) 1525 373178/853800
Fax: +44 (0) 1525 851319
Lo-call Tel: 0845 3108053
E-mail: info@calex.co.uk
Online: <http://www.calex.co.uk>