

Details of Multi Blade Sets



(F1571581)

F1571581 - English

Multi blade adapter set – 35 pcs

- universal set ideal for repair and maintenance of miniature components in electrical and electronic

industries, for audio/visual, office equipment, service etc.

- hardened & tempered high carbon steel blades

- adapters made of special tool steel

- set is being supplied in a useful vinyl pouch

- Contents: 2 pieces ¼" hex drive chuck-style adapters

33 metric blades – 1 piece each:

Slotted: 0,6 / 1,0 / 1,4 / 1,8 / 2,0 and 2,5 mm

Phillips: sizes 000 / 00 / 0 and 1

JIS Type S: sizes 000 / 00 / 0 and 1

for Torx®: sizes T3 / T4 / T5 / T6 / T7 / T8 / T9 / T10 (sizes T8 and 10 are

Tamperproof)

Hexagon: 0,7 / 0,9 / 1,3 / 1,5 / 2,0 and 2,5 mm

Nut Drivers: 2,0 / 2,5 / 3,0 / 3,5 and 4,0 mm



(F1571604)

F1571604 - English

Multi Blade Screwdriver Set – 28 pcs

- universal set ideal for repair and maintenance of miniature components in electrical and electronic

industries, for audio/visual, office equipment, service etc.

- hardened & tempered high carbon steel blades

- handle made from steel with nickel plated finish

- set is being supplied in a useful vinyl pouch

- Contents: 1 screwdriver handle with chuck to take blades

27 blades – 1 piece each:

Slotted: .025" (0,64 mm) / .040" (1,02 mm) / .055" (1,4 mm) / .070" (1,78 mm) /
.080" (2,03 mm) and .100" (2,54 mm)

Phillips: sizes 0 and 1

Hexagon: .028" / .035" / .050" / .062" / .078" and 0.93"

Nut Drivers: 5/64", 3/32", 7/64", 1/8" and 5/32"

Open End Wrench: 5/64", 3/32", 7/64", 1/8", 5/32", 3/16", 1/4" and 5/16"