

1567 TORX® Kraftform Micro® Screwdriver



Application: For TORX® socket screws
Blade: Round, mat nickel
Tip: TORX®, Black Point
Handle: Kraftform Micro®, multi-component grip

Code	Tip	mm	mm	mm	mm	mm	mm	mm	mm
05030120001	TX 4	40	97	2,5	1 9/16"				5
05030121001	TX 5	40	97	3,0	1 9/16"				5
05030122001	TX 6	40	97	3,0	1 9/16"				5

1569 Nutspinner



Application: For hexagon headed screws
Blade: Round, mat nickel
Tip: Hexagonal socket DIN 475/2
Handle: Kraftform Micro® with anti-roll protection and rotating cap, multi-component

Code	Tip	mm	mm	mm	mm	mm	mm	mm	mm
05030150001		5,0	60	97	7,0	2 3/8"			5
05030151001		5,5	60	97	7,8	2 3/8"			5

1567 BO Kraftform Micro® Resis-TORX® Screwdriver



Application: For tamper-resistant TORX® socket screws (BO = tamper resistant)
Blade: Round, mat nickel
Tip: TORX®-BO, Black Point
Handle: Kraftform Micro® with anti-roll protection and rotating cap; multi-component

Code	Tip	mm	mm	mm	mm	mm	mm	mm	mm
05030123001	TX 7	60	97	3,0	2 3/8"				5
05030124001	TX 8	60	97	3,0	2 3/8"				5
05030125001	TX 9	60	97	4,0	2 3/8"				5
05030126001	TX 10	60	97	4,0	2 3/8"				5

Kraftform Kompakt® 10 ESD



10 pieces set
 1 bit holder 813 R ESD Kraftform® with quick-release chuck Rapidaptor®

Code	Tip	mm	mm	mm	mm	mm	mm	mm	mm
05056677001	813 R ESD	1 x 1/4"x90							1
	800/1 TZ	1 x 0,5x4,0x25; 1 x 1,0x5,5x25							
	851/1 TZ PH	1 x PH 1x25; 1 x PH 2x25							
	855/1 TZ PZ	1 x PZ 1x25; 1 x PZ 2x25							
	867/1 TZ TORX®	1 x TX 10x25; 1 x TX 15x25; 1 x TX 20x25							

1578 A Kraftform Micro® Slotted Screwdriver



Application: For slotted screws
Blade: Round, mat nickel
Tip: DIN 8320 up to 0,3 x 1,8, DIN 5264-A as of 0,4 x 2,0, ISO 2380 as of 0,4 x 2,0, Black Point
Handle: Kraftform Micro® with anti-roll protection and rotating cap; multi-component

Code	Tip	mm	mm	mm	mm	mm	mm	mm	mm
05030100001		0,25	1,2	40	97	2,5	0,05"	1 9/16"	5
05030101001		0,23	1,5	40	97	2,5	1/16"	1 9/16"	5
05030102001		0,30	1,8	60	97	2,5	0,07"	2 3/8"	5
05030103001		0,40	2,0	60	97	2,5	5/64"	2 3/8"	5
05030104001		0,40	2,5	80	97	2,5	3/32"	3 1/8"	5
05030105001		0,50	3,0	80	97	3,0	1/8"	3 1/8"	5
05030106001		0,60	3,5	80	97	4,0	9/64"	3 1/8"	5
05030107001		0,80	4,0	80	97	4,0	5/32"	3 1/8"	5

Kraftform Kompakt® 11 ESD



10 pieces set
 1 bit holder 813 R ESD Kraftform® with quick-release chuck Rapidaptor®

Code	Tip	mm	mm	mm	mm	mm	mm	mm	mm
05056678001	813 R ESD	1 x 1/4"x90							1
	800/1 Z	1 x 0,5x3,0x25							
	851/1 TZ PH	1 x PH 1x25							
	851/1 Z PH	1 x PH 0x25							
	867/1 TZ TORX®	1 x TX 5x25; 1 x TX 6x25; 1 x TX 7x25; 1 x TX 8x25; 1 x TX 9x25; 1 x TX 10x25							