



#### Flexible high pressure washers for outdoor cleaning tasks

The C 120.3 high pressure washer is ideal for all types of low frequency outdoor cleaning tasks. Its trolley is designed for easy storage of all the standard accessories. This model is also available in a max. 125 bar variant, C 125.3, with a 1800W motor.

The C 120.3 offers incredible mobility and flexibility. It is perfect for anyone who needs a basic ergonomic pressure washer with high performance. With the Click&Clean (C&C) system it is quick and easy to change nozzles, and the standard Nilfisk bayonet coupling ensures compatibility to the large Nilfisk accessory range.

#### PRODUCT FACTS

- Reliable aluminium pump
- Pressure regulation
- Click&Clean system ensures a quick change of nozzles
- Automatic start/stop
- Light weight makes it easy to handle
- "PA" models include Patio Plus and a washing brush
- "PAD" models include Patio Plus, washing brush, 15 m drain and tube tube cleaner
- "PC" models include Compact patio cleaner
- Handle with quick coupling and swivel of hose
- Hook for storage of hose and cable

Model	C 120.3-6
Ref. no	128470015
Description	C120.3-6 UK
<b>PRODUCT FEATURES</b>	
AUTOMATIC START/STOP	■
CABLE STORAGE	■
TROLLEY	■
PRESSURE REGULATION	■
CLICK & CLEAN (C&C) NOZZLE CONCEPT	■
ALUMINIUM PUMP	■
GUN WITH QUICK CONNECTION AND SWIVEL	■
LANCE AND SPRAY GUN STORAGE	■
STORAGE OF ACCESSORIES	■
<b>INCL. ACCESSORIES</b>	
6520844 CLEANING TOOL	■
6411132 CLICK & CLEAN FOAM SPRAYE	■
126411158 COMPACT PATIO	
6410766 DRAIN/TUBE CLEANER 15M	
126481132 G3 GUN WITH INTERMEDIATE	■
126481134 G3 LANCE COMPLETE	■
126481138 HOSE 6M	■
126481139 HOSE 8M	
126411795 Long fixed brush	
126411376 PATIO CLEANER PLUS ACC	
126481115 POWERSPEED	■
126481120 PR TORNADO DARK	■

Technical specifications	C 120.3-6
CABLE LENGTH (M)	5
VOLTAGE (V)	230
MOTOR RATED POWER (KW)	1.7
POWER CONSUMPTION (A)	7.5
WATER FLOW QMAX/QIEC (L/H)	520/350
PUMP PRESSURE (BAR/MPA)	Max. 120/12
HOSE LENGTH (M)	6
MAX INLET TEMPERATURE (°C)	40
DIMENSIONS LXWXH (MM)	280x250x850
WEIGHT (KG)	8.9