



An all-round pressure washer with a high performance

The E 130.2 is a domestic pressure washer, which offers, along with a good performance level, a high level of comfort, flexibility and user-friendliness. For all types of medium to high frequency cleaning tasks around the house.

The E 130.2 is very mobile, due to an upright and ergonomic design plus the extra handle for lifting and the built in telescopic handle make it easy to store away as a compact unit. The storage options include storage of Click&Clean (C&C) auto brush or a rotary brush. The height of the products ensure good ergonomics. The C&C nozzle system makes it quick and easy to change the nozzles. The standard Nilfisk bayonet coupling ensures compatibility to the Nilfisk consumer accessories range. It is standard with a reliable and long lasting induction motor. It can be stored and used as a stationary solution on the wall by separate wall-hook.

PRODUCT FACTS

- Reliable aluminium pump
- Telescopic handle with sturdy and robust aluminium tubes
- Trolley for high mobility
- Storage of gun, nozzle and foam sprayer
- Integrated storage for hose and electric cable
- Pressure regulation
- Click&Clean nozzle system ensures quick and easy change of nozzle
- Automatic start/stop
- Sturdy and robust design
- Noise reduction by rubber suspension of motor pump unit
- Can be used as stationary solution with a separate wall hook.

Model	E 130.2-8
Ref. no	126531613
Description	E130.2-8 UK

PRODUCT FEATURES

AUTOMATIC START/STOP	■
CABLE STORAGE	■
SOFT GRIP	■
TROLLEY	■
PRESSURE REGULATION	■
HOSE REEL	
CLICK & CLEAN (C&C) NOZZLE CONCEPT	■
ALUMINIUM PUMP	■
GUN WITH QUICK CONNECTION AND SWIVEL	■
LANCE AND SPRAY GUN STORAGE	■
STORAGE OF ACCESSORIES	■


INCL. ACCESSORIES

6520844 CLEANING TOOL	■
6411132 CLICK & CLEAN FOAM SPRAYE	■
126481146 G4 GUN WITH INTER.TUBE	■
126481139 HOSE 8M	■
126481115 POWERSPEED	■
126481117 PR TORNADO	■
126411395 ROTARY BRUSH	

Technical specifications E 130.2-8

CABLE LENGTH (M)	5
VOLTAGE (V)	230
MOTOR RATED POWER (KW)	2.1
POWER CONSUMPTION (A)	9
WATER FLOW QMAX/QIEC (L/H)	500-450
PUMP PRESSURE (BAR/MPA)	Max. 130 / Max. 13
HOSE LENGTH (M)	8
MAX INLET TEMPERATURE (°C)	60
DIMENSIONS LXWXH (MM)	360x340x900
WEIGHT (KG)	17.7

Accessories	Ref. no	Min. required	E 130.2-8
	Options		
NILFISK BA VALVE COMPLETE	106411177	1	■
	Consumer pressure washer acc.		
WATER FILTER	106411231	1	■
GARDEN BRUSH	106411325	1	■
RIM BRUSH	106411326	1	■
HEAD FOR GARDEN BRUSH	106411327	1	■
HEAD FOR RIM BRUSH	106411328	1	■
7M HP HOSE EXCELLENT	106411346	1	■
WALL HOOK	106411386	1	■
PATIO CLEANER PLUS ACC	126411376	1	■
WATER SUCTION KIT	126411387	1	■
ROTARY BRUSH	126411395	1	■
POWERSPEED GREEN	126481115	1	■
PR TORNADO GREEN	126481117	1	■
G3 LANCE COMPLETE	126481134	1	■
HOSE 6M	126481138	1	
HOSE 8M	126481139	1	■
HOSE 9M X-TRA MODELS	126481142	1	
HOSE 10M X-TRA MODELS	126481143	1	
G4 GUN WITH INTER.TUBE	126481146	1	■
EXTENSION HOSE 7M	6410760	1	■
ROTARY BRUSH	6410762	1	■
UNDERCHASSIS WASH LANCE	6410763	1	■
AUTO BRUSH	6410765	1	■
DRAIN/TUBE CLEANER 15M	6410766	1	■
VSB 120-1 (GREEN)	6410891	1	■
EXTENSION HOSE DYNAMIC 7M	6411048	1	■
AUTO BRUSH WITH SQUEEGEE	6411131	1	■
CLICK & CLEAN FOAM SPRAYE R	6411132	1	■
AUTO KIT CLICK & CLEAN	6411134	1	■
UNDERCHASSIS NOZZLE	6411135	1	■
AUTO NOZZLE	6411136	1	■
MULTI ANGLE ADAPTOR	6411138	1	■
CLEANING TOOL	6520844	1	■

Accessories	Ref. no	Min. required	E 130.2-8
Detergents			
 CAR COMBI CLEANER BOX 4X2 .5LTR	308000095	1	■
METAL CLEANER BOX 4 X 2.5 LTR	308000096	1	■
PLASTIC CLEANER BOX 4X 2. 5 LTR	308000097	1	■
STONE & WOOD CLEANER BOX 4X2.5	308000098	1	■
WOOD CLEANER BOX 4 X 2.5L TR	308000099	1	■