



Data sheet E08-CC4A1A-DG0200C1-XA500-AC

Industrial Connectors:Archive - Industrial Connectors:M8 Circular connector (M8 E-Series):with screw locking:Cable socket with integrally molded lead:E08-CC4A1A-DG0200C1-XA500-AC

Name	E08-CC4A1A-DG0200C1-XA500-AC
	
	Angled cable socket, with integrally molded lead, selfsecuring lock nut, cable length 2 m
Delivery informations	
Document created at	03-11-2010
Availability	available
Product description	
Description	Angled cable socket, with integrally molded lead, selfsecuring lock nut, cable length 2 m
Type	E08-CC4A1A-DG0200C1-XA500-AC
Order No.	934 556-007
Other standard types	cable length 5 m, order no. 934 556-008; cable length 10 m, order no. 934 556-009
Type of contact	female
Number of contacts	4
Cable material	PVC
Cable color	black
Cable length	2 m
Conductor size	0.25 mm ²
Cable specification	flexible lead
Cable type	LiFYY
Standard	IEC 61076-2-101 (Ed. 1)
Housing Color	black
Technical data	
Wire stranding	32 x 0.1
Rated voltage	AC/DC 60 V
Rated current	4 A, notice UL and derating
Material	
Contact material	Cu Sn
Contact surface material	Au
Contact bearer material	PA
Housing material	PUR
Coupling nut material	Zn Al/Ni
O-Ring	Viton
Environmental conditions	
Protection class (IEC 60529)	IP 65, IP 67, IP 68, IP 69K
Pollution severity	3
Temperature range	-25 °C to +90 °C, notice derating
Inflammability class	
Housing	HB
Cable	UL FT1
Contact bearer	V0
Approvals	
UL	UL
Packing unit	
Packaging unit	25 pieces

Industrial Connectors:Archive - Industrial Connectors:M8 Circular connector (M8 E-Series):with screw locking:Cable socket with integrally molded lead:E08-CC4A1A-DG0200C1-XA500-AC

Picture

Drawing

