

Value Charger

North American Region

Download Instructions and Warranty Information

[English](#) | [Français](#) | [Español](#)



Product Detail:

Designation: Value Charger

Model: CHVC2

Color: Silver

Charge Capability: "AA" (2) or (4) / "AAA" (2) or (4)
"AA" (2) and "AAA" (2) Simultaneously

Note: When charging only 2 batteries, place batteries in the two positions to the left or right.

Charging Times: (estimated)	Battery (NiMH)	Capacity (mAh)	Estimated (time)
	AA	1300-2000	8-12.5 hrs
	AA	2100-2500	13-16 hrs
	AAA	850-900	11-12 hrs

Shutoff Mechanism: None

Charging Current: "AA" 190mA
"AAA" 90mA

Trickle Charge: None

Input Rating: 120VAC, 60Hz

Input Power: 6W

Typical Weight: 184.3 grams (5.9 oz.)

Dimensions (mm): 132 x 70 x 57 (H x L x W)

Rev Polarity Protection: Yes

Primary Battery Detection: None

CONVENIENT

- Charges 2 or 4 NiMH AA's or AAA's



EASY

- LED Indicators



SLEEK

- Compact Design



ECONOMICAL

- Value Priced



CORDLESS

- Fold-out Plug



Before Using Your Charger:

Please read all instructions and cautionary markings on the battery charger, batteries, and device.

Best used with Energizer NiMH batteries.

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication.

©Energizer Holdings, Inc.

Contents herein do not constitute a warranty.